

[See all 3 Products in Family](#)

## TECHSPEC® 25.4mm Protected Gold $\lambda/10$ Knife-Edge Pickoff Mirror



25.4mm Enhanced Protected Gold  $\lambda/10$  D-Shaped Pickoff Mirror, #36-136

Stock **#36-136** **5 In Stock**

1  MRP ₹11,501

Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1-5	₹11,501 each
Qty 6-25	₹10,392 each
Qty 26+	₹9,131 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Flat Mirror **Type:**

#### Physical & Mechanical Properties

25.40 **Diameter (mm):**

**Thickness (mm):**

6.35 ±0.20

**Back Surface:**  
Fine Grind

**Bevel:**  
Protective as needed

**Dimensional Tolerance (mm):**  
+0.0/-0.20

**Edges:**  
Ground

**Parallelism (arcmin):**  
2

## Optical Properties

**Coating Type:**  
Metal

**Coating:**  
Protected Gold (700-10000nm)

**Surface Flatness (P-V):**  
λ/10

**Wavelength Range (nm):**  
700 - 10000

**Substrate:**   
[Fused Silica](#) (Corning 7980)

**Coating Specification:**  
R<sub>avg</sub> >96% @ 700 - 2000nm  
R<sub>avg</sub> >96% @ 2000 - 10,000nm

**Surface Quality:**  
20-10

**Damage Threshold, Reference:**   
0.8 J/cm<sup>2</sup> @ 1064nm, 10ns

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

**Reach 247:**  
[Compliant](#)

**Country of Origin:**  
United States

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Designed to Separate Two Beams Propagating Closely Next to Each Other
- 45° Bevel
- Coating Aperture Up to the Knife-Edge
- Enhanced Aluminum, Protected Gold and Protected Silver Coating Options

Knife-Edge Pickoff Mirrors are designed to selectively reflect an individual beam from a group of tightly spaced beams, while minimizing the overall footprint of the application. These mirrors feature a sharp 45° bevel with a reflective coating that extends to the beveled edge on a precision Fused Silica substrate with λ/10 flatness to the bevel. Knife-Edge Pickoff Mirrors are ideal for applications that incorporate dispersion prisms and diffraction gratings. These mirrors are available in three metallic coating options with performance from the visible spectrum into the far IR.

## Technical Information



---

;