

TECHSPEC®

25.4mm Inner Single Optic Mount



TECHSPEC Multi-Element Inner Single Optic Mounts

Stock #38-756 12 In Stock

-

1

+

₹2,494

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-4        | ₹2,494 each                   |
| Qty 5+         | ₹2,369 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

|                     |           |
|---------------------|-----------|
| Fixed               | Type:     |
| Optic Mount (Fixed) | Function: |

Physical & Mechanical Properties

|                                         |                    |
|-----------------------------------------|--------------------|
| Matte Black Anodized Aluminum (6061-T6) | Construction:      |
|                                         | Total Length (mm): |

|      |                                           |
|------|-------------------------------------------|
| 11   |                                           |
|      | Clear Aperture CA (mm):                   |
| 22.0 |                                           |
|      | Max. Thickness of Compatible Optics (mm): |
| 5.0  |                                           |
|      | Min. Thickness of Compatible Optics (mm): |
| 1.0  |                                           |
|      | Edge Thickness of Compatible Optics (mm): |
| 5.0  |                                           |

| Threading & Mounting |                                     |
|----------------------|-------------------------------------|
|                      | Diameter of Compatible Optics (mm): |
| 25.4                 |                                     |
|                      | Thread Type:                        |
| M29 x0.75            |                                     |

| Regulatory Compliance               |                             |
|-------------------------------------|-----------------------------|
|                                     | RoHS 2015:                  |
| Compliant                           |                             |
|                                     | Certificate of Conformance: |
| View                                |                             |
|                                     | Reach 250:                  |
| Compliant                           |                             |
|                                     | Country of Origin:          |
| China                               |                             |
|                                     | Imported By:                |
| Edmund Optics India Private Limited |                             |

## Product Details

- Mounts for a Variety of Optical Component Diameters and Thicknesses
  - M29 Outer Diameter Threads Allow Easy Positioning Within [Outer Tubes](#)
  - One Retainer Ring and One Delrin Ring are Included
  - Click [Here](#) to See How to Use the Multi-Element Tube System Components to Build an Optical System.
- TECHSPEC® Multi-Element Inner Single Optic Mounts are designed to mount a variety of optical components. The mounts support optical diameters from 5mm to 25.4mm, and edge thicknesses of 4mm to 17mm. With M29 x0.75 outer diameter threads, these mounts can be easily positioned along the optical axis of our TECHSPEC® Multi-Element Outer Tubes. TECHSPEC® Multi-Element Inner Single Optic Mounts include one Delrin ring to ensure secure clamping force between the retainer ring and optic without damaging the optic.
- Note:** Our specially designed ME Spanner Wrench ([#13-567](#)) is highly recommended to move Inner Single Optic Mounts back and forth smoothly utilizing a combined metric and English graduated scale. The hollow design enables transmission of output beam while adjusting lens position. Non-scaled ME Spanner Wrench ([#11-046](#)) is also available.