

[See all 35 Products in Family](#)

TECHSPEC® 25mm 1100-1620nm, 50R/50T, Non-Polarizing Cube Beamsplitter



Stock #47-236 **20+ In Stock**

⊖ 1 ⊕ ₹26,460

ADD TO CART

Volume Pricing	
Qty 1-5	₹26,460 each
Qty 6-25	₹21,420 each
Qty 26-99	₹19,440 each
Need More?	Request Quote

Product Downloads

General

Non-Polarizing Beamsplitter **Type:**

Physical & Mechanical Properties

Protective as needed **Bevel:**

>90 **Clear Aperture (%):**

Cube **Construction:**

25.0 x 25.0 x 25.0 ±0.1 **Dimensions (mm):**

Optical Properties

≤2 **Beam Deviation (arcmin):**

Telecom **Coating:**

R_{avg} <0.5% @ 1100 - 1620nm **Coating Specification:**

50/50 **Reflection/Transmission Ratio (R/T):**

N-BK7 **Substrate:**

40-20 **Surface Quality:**

1100 - 1620 **Wavelength Range (nm):**

<6% **|Ts-Tp|:**

45 ±10 **Absolute Transmission (%):**

45 ±5 **Average Transmission (%):**

1.25 **Power (fringes) @ 632.8nm:**

0.25 **Irregularity (fringes) @ 632.8nm:**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Compliant **REACH 241:**

Singapore **Country of Origin:**

Edmund Optics India Private Limited **Imported By:**

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Low Polarization Dependence: |Ts-Tp|<6%
- Constructed from High Tolerance Right Angle Prisms
- BBAR Coated Faces for Maximum Efficiency
- C-Mounted Visible and NIR [Cube Beamsplitters](#) Also Available

TECHSPEC® Broadband Non-Polarizing Cube Beamsplitters consist of a pair of precision high tolerance [right angle prisms](#) cemented together with a metallic dielectric coating on the hypotenuse of one of the prisms. The low polarization dependence of the metallic dielectric hybrid coating allows the transmission and reflection of S- and P-polarization states to be within 6% of each other. These beamsplitters feature anti-reflection (AR) coatings to maximize transmission across wavelengths ranging from 400-1620nm. TECHSPEC® Broadband Non-Polarizing Cube Beamsplitters are spectrally flat across their specified wavelength ranges, reducing effects caused by changes in the angle of incidence or converging/diverging beams. These beamsplitters are ideal for applications that require splitting of light, such as interferometers and polarimeters.

Technical Information

Telecom Non-Polarizing Beamsplitters

