

2.5mm CA NIR, Corning® Varioptic® A-PE Series Variable Focus Liquid Lens Development Kit



Corning® Varioptic® A-PE Series Variable Focus Liquid Lenses



Stock **#73-560** **4 In Stock**

-

1

+

₹86,580

ADD TO CART

Volume Pricing	
Qty 1+	₹86,580 each
Need More?	Request Quote

Product Downloads

General

Type:

Development Kit

Contents of Kit:

Corning® Varioptic® A-PE-25H1-33 Lens
USB-MFlexiboard (with 4 and 6 pin connector and USB compatibility)
USB-B to USB-A Cable Focuslab Software
Control Software Documentation Package

D-APE-25H1-33	Model Number:
Compact optical systems such as barcode readers, industrial cameras, & medical imaging and biometrics systems	Typical Applications:
Physical & Mechanical Properties	
8.80 (packaged lens)	Diameter (mm):
2.5	Clear Aperture CA (mm):
2.80 (packaged lens)	Thickness (mm):
Optical Properties	
NIR	Coating:
-5 to +13 diopter	Focus Range (mm):
96 @ 850nm	Transmission (%):
30nm	Transmitted Wavefront Error, RMS:
Environmental & Durability Factors	
-30 to +60	Operating Temperature (°C):
-40 to +85	Storage Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:
France	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Combine a Liquid Lens with Dedicated, Calibrated Driver Board
- Temperature Compensation and Response Time Optimization Features
- Include Control Software and Documentation Package
- [A-P Series Liquid Lenses](#) Also Available

Corning® Varioptic® A-PE & V-PE Series Variable Focus Liquid Lens Development Kits feature a variable focus liquid lens with a dedicated, calibrated driver board for enhanced performance, temperature compensation, and response time optimization, as well as all necessary cables and control software for operation. The driver board enables advanced features including temperature compensation algorithms, response time optimization for optical power changes, and sweep mode which acquires clear images while the liquid lens is still in motion. The V-PE Series expands on this technology with an 8-electrode design, enabling independent control of spheres at ±24 diopters of power, cylinders at ±5 diopters of power, and axis for astigmatism correction without any moving parts, ensuring silent, reliable operation. Corning® Varioptic® A-PE & V-PE Series Variable Focus Liquid Lenses are ideal for use in barcode readers, industrial inspection, medical imaging, and biometrics applications and are fully compatible with the [AF Explorer Camera](#) for plug-and-play operation. Also included in the development kit is a documentation package with additional application information.