

[See all 12 Products in Family](#)

TECHSPEC® 25mm Dia 0.50 NA, 355nm V-Coat, Aspheric Lens



TECHSPEC® Laser Line Coated Aspheric Lenses

Stock **#33-011** **5 In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ ₹43,985

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-5 | ₹43,985 each |
| Qty 6-25 | ₹35,422 each |
| Qty 26-49 | ₹33,086 each |
| Need More? | Request Quote |

Product Downloads

General

Aspheric Lens **Type:**

Physical & Mechanical Properties

25.00 +0.0/-0.1 **Diameter (mm):**

Centering (arcmin):

| | |
|----------------------|----------------------------------|
| ≤5 | |
| 22.5 | Clear Aperture CA (mm): |
| 1.75 | Edge Thickness ET (mm): |
| 9.75 ±0.1 | Center Thickness CT (mm): |
| Protective as needed | Bevel: |
| Plano | Shape of Back Surface: |

Optical Properties

| | |
|---|--|
| 25.00 @ 587.6nm | Effective Focal Length EFL (mm): |
| 0.50 | Numerical Aperture NA: |
| 18.32 | Back Focal Length BFL (mm): |
| Fused Silica (Corning 7980) | Substrate: <input type="checkbox"/> |
| 355 | Aspheric Design Wavelength (nm): |
| 1.2λ | Asphere Figure Error, RMS @ 632.8nm: |
| Laser V-Coat (355nm) | Coating: |
| R _{abs} <0.25% @ 355nm | Coating Specification: |
| 60-40 | Surface Quality: |
| 1.00 | f#: |
| Infinite | Conjugate Distance: |
| 7.5 J/cm ² @ 355nm, 20ns, 20Hz | Damage Threshold, By Design: <input type="checkbox"/> |
| 40.00 | Power (diopters): |


Regulatory Compliance

| | |
|-------------------------------------|------------------------------------|
| Compliant | RoHS 2015: |
| View | Certificate of Conformance: |
| Compliant | Reach 235: |
| Japan | Country of Origin: |
| Edmund Optics India Private Limited | Imported By: |

Product Details

- Designed and Coated for Nd:YAG Laser Wavelengths
- High Laser Damage Thresholds
- Low Coefficient of Thermal Expansion

TECHSPEC® Laser Line Coated Aspheric Lenses are designed to maximize performance in high power Nd:YAG laser applications. The aspheric designs minimize spherical aberration to decrease laser spot size and maintain high power per area. Additionally, TECHSPEC® Laser Line Coated Aspheric Lenses feature high performance coatings that have been optimized for the most popular Nd:YAG laser wavelengths and a high damage threshold, UV fused silica substrate that is highly resistant to thermal expansion.



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness

- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts
