



[See all 4 Products in Family](#)

## TECHSPEC® 25mm Dia., 355nm, Stemmed Laser Mirror



Stock #17-559 CLEARANCE [CONTACT US](#)

1 MRP ₹12,712

Price inclusive of all taxes

[ADD TO CART](#)

### Volume Pricing

Qty 1+	₹12,712 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Type:  
Stemmed Mirror

Compatible Kinematic Mount:  
[#58-853](#)

#### Physical & Mechanical Properties

Thickness (mm):  
13.00 ±0.20

22.50	<b>Clear Aperture CA (mm):</b>
25.00 +0.00/-0.10	<b>Diameter (mm):</b>
90.00	<b>Clear Aperture (%):</b>
Commercial Polish	<b>Back Surface:</b>
Ground, protective bevel as needed	<b>Edges:</b>
12.50 +0.00/-0.10	<b>Stem Diameter (mm):</b>
6.50 ±0.20	<b>Stem Length (mm):</b>

## Optical Properties

Fused Silica (Corning 7980)	<b>Substrate:</b> <input type="checkbox"/>
10-5	<b>Surface Quality:</b>
Laser Mirror (355nm)	<b>Coating:</b>
355	<b>Design Wavelength DWL (nm):</b>
M10	<b>Surface Flatness (P-V):</b>
R <sub>abs</sub> >99.8% @ 355nm	<b>Coating Specification:</b>
Dielectric	<b>Coating Type:</b>
7.5J/cm <sup>2</sup> @ 20ns, 20Hz @ 355nm	<b>Damage Threshold, Reference:</b> <input type="checkbox"/>
7.5J/cm <sup>2</sup> @ 20ns, 20Hz @ 355nm	<b>Damage Threshold, Pulsed:</b>

## Regulatory Compliance

<a href="#">View</a>	<b>Certificate of Conformance:</b>
United States	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).



## Product Details

- Stemmed Design Reduces Stress on Mirror Surface when Mounted by Stem
- >99% Reflectivity at Standard Laser Wavelengths
- 10-5 Surface Quality for Reduced Scatter in Sensitive Laser Applications
- TECHSPEC® [Broadband Dielectric](#) and [Metallic Coated](#) Stemmed Mirrors Also Available


TECHSPEC® Stemmed Laser Mirrors provide low mounting stress on highly reflective, laser line mirrors. Designed to be mounted to TECHSPEC® [Kinematic Circular Optical Mounts](#) and [E-Series Kinematic Optical Mirror Mounts](#), all contact between the mirror and the kinematic mount is through the stem, reducing the stress imparted on the optical surface of the mirror. Due to their stress-reducing design and monolithic fused silica construction, these mirrors provide excellent thermal stability and improved surfaced flatness compared to traditionally mounted M10 flat mirrors. TECHSPEC® Stemmed Laser Mirrors are available at common laser wavelengths, making them ideal for laboratories and integration in laser systems.

**Note:** Contact us for custom options.

## Technical Information



A comparison of the aberrations introduced to a  $\lambda/10$  Stemmed Mirror and a  $\lambda/10$  First Surface Mirror when mounted in a kinematic mount. As shown, a Stemmed Mirror stays within  $\lambda/10$  specification up to 12 in-oz of torque ("hand-tight") while a First Surface Mirror becomes out of specification with a surface flatness of  $\lambda/5$ .



Stemmed Mirrors are mounted to kinematic mounts by a stem on their back surface, resulting in no contact with the edges of the mirror surface.