

[See all 5 Products in Family](#)

**TECHSPEC® 25mm Dia. 400 - 750nm Broadband  $\lambda/4$  Mirror**



Broadband Dielectric  $\lambda/4$  Mirrors

Stock **#70-671** **20+ In Stock**

- 1 + MRP ₹9,383

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹9,383 each
Qty 6-25	₹7,466 each
Qty 26-49	₹7,012 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Flat Mirror **Type:**

**Physical & Mechanical Properties**

25.00 +0.00/-0.25 **Diameter (mm):**

**Thickness (mm):**

3.00 ±0.25

Commercial Polish **Back Surface:**

90 **Clear Aperture (%):**

22.50 **Clear Aperture CA (mm):**

Ground **Edges:**

5 **Parallelism (arcmin):**

## Optical Properties

Dielectric **Coating Type:**

Dielectric Mirror (400-750nm) **Coating:**

$\lambda/4$  (typical) **Surface Flatness (P-V):**

400 - 750 **Wavelength Range (nm):**

**BOROFLOAT®** **Substrate:**

0-45 **Angle of Incidence (°):**

**Coating Specification:**  
R<sub>avg</sub> >98% @ 400 - 750nm (0-45°, All Polarizations)  
R<sub>avg</sub> >99% @ 400 - 750nm (0-45°, S-Polarizations)

60-40 **Surface Quality:**

**Damage Threshold, By Design:**   
0.5 J/cm<sup>2</sup> @ 532nm, 20ns, 20Hz

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

United States **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91-80-6845 0000

## Product Details

- Enhanced Reflectivity and LDT over Metallic Coatings
- Average Reflectivity >99% from 400 – 750nm
- Designed for all Polarization States at 0 – 45° AOI
- [λ/10](#) Versions Available

TECHSPEC® Broadband Dielectric  $\lambda/4$  Mirrors feature a high laser damage threshold of 0.5 J/cm<sup>2</sup> @ 532nm, 20ns pulse, at 20Hz as well as a >99% reflection from 400 – 750nm across all polarization states. Constructed from highly durable BOROFLOAT® substrates, these mirrors feature outstanding thermal and high chemical durability making them ideal for high temperature and harsh environment applications. TECHSPEC® Broadband Dielectric  $\lambda/4$  Mirrors are available in a variety of diameters from 12.5 - 50mm. A low-cost alternative to our precision polished [TECHSPEC Broadband Dielectric  \$\lambda/10\$  Mirrors](#), these mirrors are ideal for spectroscopy, microscopy, and general laboratory use such as beam steering or reflection applications utilizing multiple laser sources.

**Note:** Surface Flatness is measured pre-coating and deviations may appear after the coating has been applied. For applications where surface flatness is critical it is recommended to use the [TECHSPEC® Broadband Dielectric  \$\lambda/10\$  Mirrors](#).