


25mm Dia. High Contrast IR Polarizer



Stock #36-655 **1 In Stock**

- 1 + MRP ₹1,00,386

● Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-9	₹1,00,386 each
Qty 10+	₹95,342 each
Need More?	Request Quote

Product Downloads

General

Linear Polarizer **Type:**

Physical & Mechanical Properties

22.50 **Clear Aperture CA (mm):**

25.00 **Diameter (mm):**

Thickness (mm):

2.00 ±0.2

+0.0/-0.2

Dimensional Tolerance (mm):

Construction:

Nanoparticle

Clear Aperture (%):

90

Optical Properties

Angle of Incidence (°):

±20

Extinction Ratio:

>100,000:1 (900nm - 1200nm)
>10,000:1 (750nm - 1400nm)
>1,000:1 (650nm - 1700nm)

Substrate:

Soda Lime Float Glass

Transmission (%):

>80

Transmitted Wavefront, P-V:

< λ/4

Beam Deviation (arcmin):

<1

Polarization Axis Mark (%):

±2

Wavelength Range (nm):

650 - 1700

Environmental & Durability Factors

Operating Temperature (°C):

-20 to +120

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

REACH 241:

[Compliant](#)

Country of Origin:

Germany

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Multiple Wavelength Ranges for UV, VIS and NIR
- >100,000:1 Contrast Ratios Available
- Ideal for Use in Harsh Environments

UV, VIS-NIR, and NIR High Contrast Polarizers offer both versatility and performance over a wide range of wavelengths. These polarizers contain uniformly stretched silver nano-particles in a 220 ±25µm thick soda-lime glass laminated on a thicker soda-lime substrate for increased durability. UV, VIS-NIR, and NIR High Contrast Polarizers are ideal for harsh environments, can withstand up to 120°C, are resistant to UV-radiation and chemicals, and can be safely used in humid environments.

Technical Information

