

[See all 16 Products in Family](#)

TECHSPEC® 25mm Dia. x 20mm FL, Uncoated, Hybrid Asphere



TECHSPEC® Plastic Hybrid Aspheric Lenses

Stock **#21-225** **20+ In Stock**

[Other Coating Options](#)

-

1

+

₹6,812

ADD TO CART

Volume Pricing	
Qty 1-24	₹6,812 each
Qty 25-99	₹5,177 each
Qty 100-249	₹3,970 each
Need More?	Request Quote

Product Downloads

General

Aspheric Lens

Type:

Physical & Mechanical Properties

25.00 ±0.15

Diameter (mm):

Clear Aperture CA (mm):

23.00	
	Edge Thickness ET (mm):
3.4	
	Center Thickness CT (mm):
10.00 ±0.20	
	Bevel:
Protective as needed	
	Shape of Back Surface:
Convex	

Optical Properties	
	Effective Focal Length EFL (mm):
20.00 @ 587.6nm	
	Numerical Aperture NA:
0.63	
	Back Focal Length BFL (mm):
13.89	
	Substrate: □
Zeonex K22R	
	Aspheric Design Wavelength (nm):
587.6	
	Coating:
Uncoated	
	Surface Quality:
80-50	
	f/#:
0.8	
	Radius R ₂ (mm):
127	
	Wavelength Range (nm):
475 - 675	
	Conjugate Distance:
Infinite	

Environmental & Durability Factors	
	Operating Temperature (°C):
-30 to +70	
Regulatory Compliance	
	Certificate of Conformance:
View	
	Country of Origin:
United States	
	Imported By:
Edmund Optics India Private Limited	

Product Details


- Color-Corrected Plastic Aspheres
- Diffractive Surface Minimizes Chromatic Aberration
- Low-Cost, Molded Design

TECHSPEC® Plastic Hybrid Aspheric Lenses are molded aspheric lenses with diffraction-limited designs that eliminate chromatic aberrations caused by broadband light sources. These hybrid aspheric lenses are ideal for imaging or ophthalmic applications, or for use with tunable lasers or broadband or multispectral illumination sources. The [aspheric lens](#) eliminates spherical aberration, while the diffractive surface features a negative optical dispersion to yield excellent color correction.

TECHSPEC Plastic Hybrid Aspheric Lenses are similar in performance, but offer several advantages to our [TECHSPEC Aspherized Achromatic Lenses](#). Hybrid aspheric lenses feature all-plastic, monolithic designs that are much lighter than comparable aspherized achromatic lenses. These optical lenses are also available in higher numerical apertures. However, plastic hybrid aspheric lenses are limited by the inherent diffraction efficiency of the aspheric surface, yielding lower overall transmission than comparable aspherized achromatic lenses.

These lenses won the 2011 Prism Award for Optics and Optical Components.

Technical Information



Monochromatic Spot Size Comparison for
25mm Diameter f/1.2 Optical Components

