

TECHSPEC<sup>®</sup> 25mm Dia x 20mm FL, VIS-EXT Coated Molded Aspheric Condenser Lens



TECHSPEC Molded Aspheric Condenser Lenses

Stock **#71-087** **9 In Stock**

[Other Coating Options](#)

-

1

+

₹4,671

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | ₹4,671 each                   |
| Qty 11-25      | ₹4,204 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

SPECIFICATIONS

General

Type:

Condenser Lens

Note:

[Click here](#) for more information on the ISO 10110

|                                                                   |                                  |
|-------------------------------------------------------------------|----------------------------------|
| surface quality specification.                                    |                                  |
| Physical & Mechanical Properties                                  |                                  |
| 25.00 +0.0/-0.2                                                   | Diameter (mm):                   |
| ≤25                                                               | Centering (arcmin):              |
| 22.28                                                             | Clear Aperture CA (mm):          |
| 3.21                                                              | Edge Thickness ET (mm):          |
| 12.27 ±0.30                                                       | Center Thickness CT (mm):        |
| Protective as needed                                              | Bevel:                           |
| 25.00                                                             | Diameter of Asphere (mm):        |
| Plano                                                             | Shape of Back Surface:           |
| Optical Properties                                                |                                  |
| 20.00 @ 587.6nm                                                   | Effective Focal Length EFL (mm): |
| 0.625                                                             | Numerical Aperture NA:           |
| 11.93                                                             | Back Focal Length BFL (mm):      |
| Liba2000+                                                         | Substrate: <input type="text"/>  |
| ±5                                                                | Focal Length Tolerance (%):      |
| VIS-EXT (350-700nm)                                               | Coating:                         |
| R <sub>avg</sub> ≤0.4% @ 425 - 675nm                              | Coating Specification:           |
| Molded Side: 5/3 x 0.4; E 0.2<br>Polished Side: 5/3 x 0.25; E 0.2 | Surface Quality:                 |
| 0.8                                                               | f/#:                             |
| ∞                                                                 | Radius R <sub>2</sub> (mm):      |
| 350 - 700                                                         | Wavelength Range (nm):           |
| Infinite                                                          | Conjugate Distance:              |
| Regulatory Compliance                                             |                                  |
| View                                                              | Certificate of Conformance:      |

## PRODUCT DETAILS

- High Numerical Apertures
- Fully Documented for OEM Integration
- Ideal for Illumination Applications

TECHSPEC® Molded Aspheric Condenser Lenses have been designed for integration into the illumination path of OEM instrumentation. Available in 5 to 50mm diameters, the small diameter lenses are ideal for medical devices or portable instruments, while the larger lenses are typically integrated into benchtop analytical equipment including biotech instruments such as DNA sequencers and polymerase chain reaction (PCR) testing platforms. The front aspheric surface is molded to eliminate spherical aberrations, while the second surface is ground and polished for improved performance. Full prescription data and drawings are available to aid in design integration.

**Note:** For custom coating options, please [contact us](#).

## CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

