


[See all 8 Products in Family](#)

25mm Dia. x 2mm Thickness Uncoated, Sodium Chloride Window



Stock **#68-815** **6 In Stock**

-

1

+

₹5,208

ADD TO CART

Volume Pricing	
Qty 1-10	₹5,208 each
Qty 11-25	₹4,694 each
Qty 26-49	₹4,401 each
Need More?	Request Quote

Product Downloads

General	
Protective Window	Type:
Physical & Mechanical Properties	
25.00 ±0.50	Diameter (mm):
2.00 ±0.50	Thickness (mm):

±0.50	Dimensional Tolerance (mm):
Protective as needed	Bevel:
Fine Ground	Edges:
0.25	Poisson's Ratio:
39.98	Young's Modulus (GPa):
18.20	Knoop Hardness (kg/mm ²):

Optical Properties	
Uncoated	Coating:
Sodium Chloride (NaCl)	Substrate: ☐
1.544	Index of Refraction (n _d):
60-40	Surface Quality:
42.89	Abbe Number (v _d):
250 - 16000	Wavelength Range (nm):


Material Properties	
2.17	Density (g/cm ³):
44	Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):
35.70	Solubility, in 100g of H ₂ O @273K (g):

Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 219:
View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Excellent Transmission from 250nm – 16µm
 - Low Cost
 - Ideal for FTIR Spectroscopy
 - [Potassium Bromide \(KBr\) Windows](#) Also Available
- Sodium Chloride (NaCl) Windows are ideal for FTIR spectroscopy. Sodium Chloride (NaCl) is a material commonly used in FTIR spectroscopy. NaCl is a relatively low-cost cubic crystalline material that has excellent transmission from 250nm – 16µm. Sodium Chloride (NaCl) Windows, over this large spectral range, have an index of refraction that ranges between 1.4 - 1.6. It is hygroscopic by nature and thus samples should not contain water. The windows are sensitive to thermal shock but can be used in temperatures up to 400°C. NaCl has a density of 2.17 g/cm3 and a Knoop Hardness of 18.2.

Technical Information



Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

Compatible Mounts