

[See all 30 Products in Family](#)

TECHSPEC®

25mm Dia. x 35mm FL Uncoated Calcium Fluoride PCX Lens



TECHSPEC Calcium Fluoride Plano-Convex (PCX) Lenses

Stock **#88-163** 13 In Stock

-

1

+

₹14,947

ADD TO CART

Volume Pricing	
Qty 1-5	₹14,947 each
Qty 6-25	₹11,989 each
Qty 26-49	₹11,288 each
Need More?	Request Quote

Product Downloads

General

Plano-Convex Lens

Type:

Physical & Mechanical Properties

25.00 +0.00/-0.10

Diameter (mm):

<3

Centering (arcmin):

7.50 ±0.1	Center Thickness CT (mm):
1.59	Edge Thickness ET (mm):
22.5	Clear Aperture CA (mm):
Protective as needed	Bevel:

Optical Properties

35.00 @ 266nm	Effective Focal Length EFL (mm):
29.87	Back Focal Length BFL (mm):
Uncoated	Coating:
Calcium Fluoride (CaF ₂)	Substrate: □
40-20	Surface Quality:
λ	Power (P-V) @ 632.8nm:
λ/2	Irregularity (P-V) @ 632.8nm:
16.17	Radius R ₁ (mm):
1.4	f/#:
0.36	Numerical Aperture NA:
200 - 7000	Wavelength Range (nm):
Random	Axis Orientation:


Regulatory Compliance

Compliant	RoHS 2015:
Compliant	Reach 219:
View	Certificate of Conformance:
South Korea	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Low Index of Refraction
 - Vacuum Grade UV Substrate
 - Uncoated, VIS-NIR, and NIR II Broadband AR Coating Options
- TECHSPEC® Calcium Fluoride Plano-Convex Lenses are ideal for demanding applications that require superior performance from the ultraviolet through the mid-wave infrared spectra. The lenses' low refractive index, high laser damage threshold, and low axial and radial-stress birefringence are highly suitable for use with Excimer lasers or for integration into infrared systems. Additionally, calcium fluoride features low solubility and offers superior hardness to comparable fluoride-based substrates, making these PCX lenses capable of withstanding harsh environments and exposure to the elements. TECHSPEC® Calcium Fluoride Plano-Convex Lenses are offered in 12.5mm, 25mm, and 50mm diameters. The lenses are available uncoated, VIS-NIR, or with NIR II broadband AR coating options.

Technical Information



Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

Compatible Mounts