

[See all 33 Products in Family](#)

**TECHSPEC® 25mm Dia x 25mm FL, V-Coated, High Precision Aspheric Lens**



TECHSPEC® High Precision Aspheric Lenses

Stock **#22-941** **9 In Stock**

[Other Coating Options](#)

1 MRP ₹80,612

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹80,612 each
Qty 6-10	₹72,541 each
Qty 11+	₹67,698 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Aspheric Lens **Type:**

3D Surface Profile not included with coated lenses **Note:**

**Physical & Mechanical Properties**

25.00 +0.0/-0.025	<b>Diameter (mm):</b>
<2.5	<b>Centering (arcmin):</b>
22.5	<b>Clear Aperture CA (mm):</b>
4.25	<b>Edge Thickness ET (mm):</b>
8.50 ±0.1	<b>Center Thickness CT (mm):</b>
Protective as needed	<b>Bevel:</b>
Plano	<b>Shape of Back Surface:</b>

## Optical Properties

25.00 @ 1550nm	<b>Effective Focal Length EFL (mm):</b>
0.50	<b>Numerical Aperture NA:</b>
20.18 @ 1500nm	<b>Back Focal Length BFL (mm):</b>
<b>N-SF6</b>	<b>Substrate:</b> <input type="checkbox"/>
1550	<b>Aspheric Design Wavelength (nm):</b>
λ40	<b>Asphere Figure Error, RMS @ 632.8nm:</b>
1550nm V-Coat	<b>Coating:</b>
$R_{abs} < 0.25\% @ 1550nm @ 0^\circ AOI$	<b>Coating Specification:</b>
0.016	<b>Asphere Figure Error (μm RMS):</b>
40-20	<b>Surface Quality:</b>
1	<b>f#:</b>
1550	<b>Design Wavelength DWL (nm):</b>
Infinite	<b>Conjugate Distance:</b>
1550	<b>Focal Length Specification Wavelength (nm):</b>
5 J/cm <sup>2</sup> @ 1550nm, 10ns	<b>Damage Threshold, By Design:</b> <input type="checkbox"/>
40.00	<b>Power (diopters):</b>

## Environmental & Durability Factors

ADHESION AND ABRASION AS PER MIL-PRF13830B APP C, PARAC.3.8.4 AND C.3.8.5	<b>Durability:</b>
---	--------------------

## Regulatory Compliance

<b>Compliant</b>	<b>RoHS 2015:</b>
<b>View</b>	<b>Certificate of Conformance:</b>
<b>Compliant</b>	<b>Reach 235:</b>
Singapore	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here

to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- High Precision Aspheric Surface
- 3D Surface Profiles Included with Uncoated Lenses
- Uncoated and <0.25% Reflectance V-Coat Available

TECHSPEC® High Precision Aspheric Lenses guarantee better than  $\lambda/40$  wave aspheric figure error. Achieved via precision magneto-rheological finishing (MRF), these aspheres offer high numerical apertures with diameters ranging from 15 to 50mm and are ideal for a variety of imaging and low light level applications. Each TECHSPEC High Precision Aspheric Lens is individually measured. 3D surface profiles are included with uncoated lenses. For diffraction-limited aspheres designed at specific Nd:YAG laser wavelengths, see our [TECHSPEC High Precision Laser Grade Aspheric Lenses](#).

---