

[See all 12 Products in Family](#)

TECHSPEC® 25mm Dia. x 75mm EFL, 1064nm V-Coat, Precision Laser Aspheric Lens



Stock **#23-862** **2 In Stock**

- 1 + MRP ₹69,917

i Price inclusive of all taxes

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-5 | ₹69,917 each |
| Qty 6-25 | ₹59,425 each |
| Qty 26-49 | ₹52,363 each |
| Need More? | Request Quote |

Product Downloads

Physical & Mechanical Properties

| | |
|-----------------------|----------------------------------|
| 25.00 +0.000 / -0.025 | Diameter (mm): |
| 22.5 | Clear Aperture CA (mm): |
| 3.78 | Edge Thickness ET (mm): |
| 5.50 +0.000 / -0.10 | Center Thickness CT (mm): |

| | |
|---------------------------------------------|--------------------------------------------------------------|
| Protective as needed | Bevel: |
| Plano | Shape of Back Surface: |
| Optical Properties | |
| 75.00 @ 355nm | Effective Focal Length EFL (mm): |
| 0.16 | Numerical Aperture NA: |
| 70.9 | Back Focal Length BFL (mm): |
| Fused Silica | Substrate: <input type="checkbox"/> |
| $\lambda/2$ RMS and 2.5 λ PV | Asphere Figure Error, RMS @ 632.8nm: |
| 1064 V-Coat | Coating: |
| $R_{\text{abs}} < 0.25\%$ @ 1064nm @ 0° AOI | Coating Specification: |
| 20-10 | Surface Quality: |
| 1.5 | f#: |
| 1064 | Design Wavelength DWL (nm): |
| Infinite | Conjugate Distance: |
| 15 J/cm ² @ 1064nm, 20ns, 20Hz | Damage Threshold, By Design: <input type="checkbox"/> |
| 0.35 μ m/mm per 1mm Window | Slope Error Aspheric Side: |
| <2.5 | Beam Deviation @ 587.6nm (arcmin): |
| 13.33 | Power (diopters): |

| | |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------|
| Regulatory Compliance | |
| Compliant | RoHS 2015: |
| View | Certificate of Conformance: |
| Compliant | Reach 235: |
| Singapore | Country of Origin: |
| Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000 | Imported By: |

Product Details

- Diffraction Limited at Designed Nd:YAG Laser Wavelengths
- Laser Damage Designed Coatings on UV Fused Silica Substrates
- Specified Slope Error to Guarantee Low Mid-Spatial Frequency Errors
- [High Precision Laser Grade Aspheric Lenses](#) are also Available

TECHSPEC® Precision Laser Aspheric Lenses are designed to maximize performance in high power laser applications. Featuring diffraction limited performance at their designed wavelengths these aspheric lenses are available with high laser damage threshold coatings optimized at the most common Nd:YAG laser wavelengths. With a $\lambda/2$ aspheric surface figure and 0.35 μ m/mm slope error, TECHSPEC® Precision Laser Aspheric Lenses minimize the mid-spatial frequency (MSF) errors and are ideal for integration into demanding laser processing, cutting, and additive manufacturing applications. Featuring UV fused silica substrates, these aspheres are highly durable and resistant to thermal expansion.