

[See all 12 Products in Family](#)

TECHSPEC® 25mm Dia. x 75mm EFL, 532nm V-Coat, Precision Laser Aspheric Lens



Stock #23-865 **3 In Stock**

⊖ 1 ⊕ ₹49,435

ADD TO CART

Volume Pricing	
Qty 1-5	₹49,435 each
Qty 6-25	₹42,039 each
Qty 26-49	₹37,057 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties

25.00 +0.000 / -0.025	Diameter (mm):
22.5	Clear Aperture CA (mm):
3.78	Edge Thickness ET (mm):
5.50 +0.000 / -0.10	Center Thickness CT (mm):

Protective as needed **Bevel:**
Shape of Back Surface:
Plano

Optical Properties

Effective Focal Length EFL (mm):
75.00 @ 355nm

Numerical Aperture NA:
0.16

Back Focal Length BFL (mm):
70.9

Substrate:
[Fused Silica](#)

Asphere Figure Error, RMS @ 632.8nm:
 $\lambda/2$ RMS and 2.5λ PV

Coating:
532 V-Coat

Coating Specification:
 $R_{\text{abs}} < 0.25\%$ @ 532nm @ 0° AOI

Surface Quality:
20-10

f#:
1.5

Conjugate Distance:
Infinite

Damage Threshold, By Design:
 10 J/cm^2 @ 532nm, 20ns, 20Hz

Slope Error Aspheric Side:
 $0.35 \mu\text{m/mm}$ per 1mm Window

Beam Deviation @ 587.6nm (arcmin):
<2.5

Power (diopters):
13.33

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 235:
[Compliant](#)

Country of Origin:
Singapore

Imported By:
Edmund Optics India Private Limited

Product Details

- Diffraction Limited at Designed Nd:YAG Laser Wavelengths
- Laser Damage Designed Coatings on UV Fused Silica Substrates
- Specified Slope Error to Guarantee Low Mid-Spatial Frequency Errors
- [High Precision Laser Grade Aspheric Lenses](#) are also Available

TECHSPEC® Precision Laser Aspheric Lenses are designed to maximize performance in high power laser applications. Featuring diffraction limited performance at their designed wavelengths these aspheric lenses are available with high laser damage threshold coatings optimized at the most common Nd:YAG laser wavelengths. With a $\lambda/2$ aspheric surface figure and $0.35 \mu\text{m/mm}$ slope error, TECHSPEC® Precision Laser Aspheric Lenses minimize the mid-spatial frequency (MSF) errors and are ideal for integration into demanding laser processing, cutting, and additive manufacturing applications. Featuring UV fused silica substrates, these aspheres are highly durable and resistant to thermal expansion.