

[See all 24 Products in Family](#)

## 25mm Dia x -15.5mm FL Enhanced Aluminum Coated, Convex Mirror



Stock #64-061 **10 In Stock**

- 1 + MRP ₹5,246

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹5,246 each
Qty 6-25	₹4,742 each
Qty 26-49	₹4,439 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Spherical Mirror **Type:**

### Physical & Mechanical Properties

25.00 +0.00/-0.10 **Diameter (mm):**

4.70 **Center Thickness CT (mm):**

90	<b>Clear Aperture (%)</b> :
2.07	<b>Edge Thickness ET (mm)</b> :
31.01	<b>Radius R (mm)</b> :
<b>Optical Properties</b>	
-15.50	<b>Focal Length FL (mm)</b> :
Enhanced Aluminum (450-650nm)	<b>Coating</b> :
R <sub>avg</sub> >95% @450 - 650nm	<b>Coating Specification</b> :
Metal	<b>Coating Type</b> :
±2	<b>Focal Length Tolerance (%)</b> :
<a href="#">N-BK7</a>	<b>Substrate</b> : <input type="checkbox"/>
60-40	<b>Surface Quality</b> :
450 - 650	<b>Wavelength Range (nm)</b> :
0.2 J/cm <sup>2</sup> @532nm, 10ns	<b>Damage Threshold, Reference</b> : <input type="checkbox"/>

<b>Regulatory Compliance</b>	
<a href="#">Compliant</a>	<b>RoHS 2015</b> :
<a href="#">View</a>	<b>Certificate of Conformance</b> :
<a href="#">Compliant</a>	<b>Reach 247</b> :
United States	<b>Country of Origin</b> :
<b>Imported By:</b>	
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	

## Product Details

- Variety of Diameters and Focal Lengths Available
- Enhanced Aluminum and Protected Gold Coatings
- Ideal for Imaging Systems

Convex Spherical Mirrors feature a polished plano second surface and convex first surface. Used primarily for increasing an imaging system's field of view, convex mirrors create a virtual, upright image. Shorter focal lengths provide wider fields of view, while longer focal lengths provide less distortion. Convex Spherical Mirrors with Enhanced Aluminum coatings are ideal for applications in the visible spectrum, while Protected Gold provides excellent reflection throughout the NIR, MWIR, and LWMR spectra. The mirrors are offered in 12, 25, and 50mm diameters, in a variety of wavelength ranges.

## Coating Curves