


TECHSPEC® 2.5mm Diameter, Fused Silica Half-Ball Lens



Stock #67-394 20+ In Stock

-

1

+

₹4,048

ADD TO CART

Volume Pricing	
Qty 1-10	₹4,048 each
Qty 11-49	₹3,231 each
Need More?	Request Quote

Product Downloads

General

Type:

Half-Ball Lens

Physical & Mechanical Properties

Diameter (mm):

2.50

Radius R (mm):

1.25

Radius Tolerance (µm):



±2.5

±35	Thickness Tolerance (µm):
±2.5	Diameter Tolerance (µm):
Optical Properties	
Fused Silica (Corning 7980)	Substrate: □
Uncoated	Coating:
200 - 2200	Wavelength Range (nm):
1.458	Index of Refraction (n _d):
0.625	Sphericity (µm):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:
Switzerland	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Excellent UV Transmission
 - Low Coefficient of Thermal Expansion
 - Ball and Half-Ball Options Available
- TECHSPEC® Fused Silica Ball and Half-Ball Lenses feature high transmission from 200nm to 2.2µm with a low coefficient of thermal expansion, making it ideal for the most demanding ball lens applications in the ultraviolet, visible, and near-infrared spectra. Ball lenses are commonly used for improving signal coupling between fibers, emitters, and detectors, as well as objective lenses in endoscopy and bar-code scanning applications. Half-ball lenses simplify handling and integration. TECHSPEC Fused Silica Ball and Half-Ball Lenses are uncoated with a fused silica substrate. The lenses are available in diameters ranging from 0.50 to 5.00mm.

Technical Information



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts
