

[See all 8 Products in Family](#)

## 25mm FL, Corning® Varioptic® C-C Series C-Mount Liquid Lens



Stock #91-614 **NEW** [CONTACT US](#)

- 1 + MRP ₹1,58,769

● Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1+	₹1,58,769 each
Need More?	<a href="#">Request Quote</a>

## General

C-mount Lens **Type:**

Coming® Varioptic® C-C-39N0-A1-250 Lens **Contents of Kit:**

## Optical Properties

25.00 **Focal Length FL (mm):**

200 - ∞ **Working Distance (mm):**

f/5 - f/22 **Aperture (f/#):**

VIS **Lens Wavelength Range:**

## Sensor

1.1" **Sensor Format:**

2.74 **Pixel Size (µm):**

## Threading & Mounting

C-Mount **Mount:**

## Environmental & Durability Factors

50 **Operating Temperature (°C):**

45 **Storage Temperature (°C):**

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

France **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Electronically Controllable Focus
- Ideal For Machine Vision Applications
- Compatible With Up to 1.1", 20mpx Sensors
- C-Mount for Seamless Integration into Imaging Systems

Coming® Varioptic® C-C Series C-Mount Liquid Lens Evaluation Kits feature an electronically controllable liquid lens and integrated driver electronics in a compact, C-Mount design. With rapid switching times, no moving parts, and AR-Coatings for excellent transmission in the VIS and NIR, these lenses are an ideal solution for autofocus applications demanding clarity, durability, and speed. Designed for seamless integration into C-Mount machine vision and imaging systems, the lenses are compatible with sensors up to 1.1". Coming® Varioptic® C-C Series C-Mount Variable Focus Liquid Lenses' integrated electronics allow the lenses to be powered by a simple DC supply and controlled through RS-232, I<sup>2</sup>C, or SPI interfaces. Evaluation kits include Lenses, USB-M Universal, USB Cable, and Focuslab Software Control Software and Documentation Package.