

TECHSPEC[®] 25mm Interchangeable Optic Mount



#85-717



Stock **#85-717** 5 In Stock

-

1

+

₹3,787

 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹3,787 each
Need More?	Request Quote

Product Downloads

General	
Fixed	Function:
Circular	Type of Optics:
Recommended for use with #85-641.	Note:

Physical & Mechanical Properties	
30.0	Compatible Plate Inner Diameter (mm):
25	Clear Aperture CA (mm):
30 Dia.	Dimensions (mm):
10.00	Thickness (mm):
Threading & Mounting	
25.0	Size of Compatible Optics (mm):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 233:
United States	Country of Origin:
Imported By: Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	

Product Details

- English and Metric Post Adapters
- Customizable Blank Disks
- Reducing Rings

TECHSPEC® Cage System Accessories are additional components for customizing a cage system. Reducing rings are used to decrease the inner diameter of cage system plates, and feature a thru-hole that allows one of the set screws to pass from the plate, through the ring, to the optic or optical mount. For mounting directly to [posts](#), post adapter disks feature M6 or ¼-20 tapped holes. 25mm diameter x 25mm length cage system post adapter disks can also be used to join a swivel plate pair. Blank disks are available to block optical paths, or to create customized mounts. Each blank disk features a 3mm diameter x 1mm deep centering hole for easy customization. Compatible with [#85-641](#) 30mm Side Access Plate, [#85-717](#) 25mm Interchangeable Optical Mount is equipped with a handle for easy insertion and removal from a cage setup.

Note: [#85-719](#) C-Mount Adapter fits within the inner diameter of 30mm cage system plates and features both male and female threading for easy integration with [TECHSPEC C-mount components](#).

Quick Video Demonstration

Maximize your application performance with the right products. View a quick video demonstration of TECHSPEC Cage System components: [Interchangeable Optical Mount and Side Access Mounting Plate](#).