

[See all 5 Products in Family](#)

## 25mm Sq., Extended Hot Mirror



Extended Hot Mirrors

Stock #46-387 **13 In Stock**

1  MRP ₹7,466

Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1-9	₹7,466 each
Qty 10-25	₹6,709 each
Qty 26-49	₹6,406 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Shortpass Filter **Type:**

### Physical & Mechanical Properties

3.30 ±0.2 **Thickness (mm):**

**Dimensions (mm):**

25.0 x 25.0

Clear Aperture (%):

≥85

Dimensional Tolerance (mm):

±0.5

Edges:

Seamed

Length (mm):

25.00

Width (mm):

25.00

### Optical Properties

Coating Type:

Dielectric

Coating:

Hot Mirror, 0°

Surface Flatness (P-V):

4 - 6λ

Wavelength Range (nm):

425 - 1600

Substrate:

**BOROFLOAT®**

Angle of Incidence (°):

0.00

Coating Specification:

R<sub>avg</sub> ≥90% @ 750 - 1150nm  
R<sub>avg</sub> ≥80% @ 1200 - 1600nm  
T<sub>avg</sub> ≥85% @ 425 - 675nm

Surface Quality:

80-50

### Regulatory Compliance

RoHS 2015:

**Compliant**

Certificate of Conformance:

[View](#)

Reach 247:

**Compliant**

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000


## Product Details


- Improved NIR Reflectance Over Standard Hot Mirrors
- Operating Temperatures up to 230°C
- Neutral Color for 5500K or 3200K Sources to ±250K

Extended Hot Mirrors are designed to reduce the heat in an optical system without sacrificing the system's visible output. While typical hot mirrors reflect from 750nm to approximately 1250nm, Extended Hot Mirrors further reduce heat by extending the reflection range to approximately 1750nm.

Hot mirrors are crucial in many projection and illumination systems where high levels of heat can quickly damage sensitive components. Hot mirrors are specially coated to transmit visible light while reflecting the NIR, a major contributor to heat generation. By using a hot mirror, heat levels are limited with minimum impact on the overall system performance.

## Technical Information





**Quote Your Size**

**Compatible Mounts**