

TECHSPEC®

25mm UV-VIS Coated, Fused Silica Right Angle Prism



Stock

#27-346

3 In Stock

-

1

+

₹15,480

ADD TO CART

Volume Pricing	
Qty 1-5	₹15,480 each
Qty 6-25	₹12,330 each
Qty 26-49	₹11,610 each
Need More?	Request Quote

Product Downloads

General	
Right Angle Prism	Type:
Coating on Entrance/Exit Faces	Note:

Physical & Mechanical Properties	
+0.00/-0.10	Dimensional Tolerance (mm):

	Bevel:
Protective as needed	
	Clear Aperture (%):
90	
	Length of Hypotenuse (mm):
35.40	
	Length of Legs (mm):
25.00	

Optical Properties

	Angle Tolerance (arcsec):
±15	
	Coating:
UV-VIS (250-700nm)	
	Substrate: ☐
Fused Silica (Corning 7980)	
	Surface Quality:
40-20	
	Image Orientation:
Left-Handed	
	Coating Specification:
R _{abs} ≤1.0% @ 350 - 450nm R _{avg} ≤1.5% @ 250 - 700nm	
	Ray Deviation (°):
90	
	Wavelength Range (nm):
250 - 700	
	Damage Threshold, Reference: ☐
3 J/cm ² @ 355nm, 10ns 5 J/cm ² @ 532nm, 10ns	
	Power (fringes) @ 632.8nm:
1.25	
	Irregularity (fringes) @ 632.8nm:
0.20	

Regulatory Compliance

	RoHS 2015:
Compliant	
	Certificate of Conformance:
View	
	Reach 235:
Compliant	
	Country of Origin:
Singapore	
	Imported By:
Edmund Optics India Private Limited	

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- BBAR Coatings from the UV to the NIR
- Ideal for Low Power Laser Sources
- Sizes Ranging from 5 – 25mm

TECHSPEC® Broadband Anti-Reflection (BBAR) Coated Fused Silica Right Angle Prisms bend an image path or redirect light at 90°. Featuring a broadband antireflection (BBAR) coating on both the entrance and exit surfaces, these prisms provide improved transmission efficiency compared to uncoated [UV fused silica right angle prisms](#). Manufactured from UV fused silica, these prisms feature low thermal expansion and excellent transmission through the UV, visible, and NIR spectra. TECHSPEC® Broadband Anti-Reflection (BBAR) Coated Fused Silica Right Angle Prisms are ideal for use in a wide range of scientific and industrial applications including medical devices, semiconductor inspection, and laser-based instrumentation.