

[See all 5 Products in Family](#)

25X Mitutoyo WLI Plan Apo Objective

See More by [Mitutoyo](#)



25X Mitutoyo WLI Plan Apo Objective

Stock #74-659 **NEW** 2 In Stock

MRP ₹10,77,930

i Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹10,77,930 each
Need More?	Request Quote

Product Downloads

General

378-402 **Model Number:**

Focal Length: 100mm **Compatible Tube Lens Focal Length (mm):**

Infinity Corrected **Style:**

Mitutoyo **Manufacturer:**

Note:
Designed to be used with a 100mm Tube Lens, Sold Separately

Physical & Mechanical Properties

Length (mm):
57.00

Maximum Diameter (mm):
40.00

Weight (g):
290.00

Optical Properties

Horizontal Field of View, 2/3" Sensor:
0.35mm

Focal Length FL (mm):
4.00

Magnification:
25X

Numerical Aperture NA:
0.50

Resolving Power (μm):
0.55

Depth of Field (μm):
1.10

Working Distance (mm):
3.60

Field Number (mm):
11.00

Parfocal Length (mm):
60.00

Sensor

Maximum Sensor Format:
2/3"

Threading & Mounting

Mounting Threads:
RMS/20.32mm x36 TPI

Regulatory Compliance

Certificate of Conformance:
[View](#)

Country of Origin:
Japan

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91-80-6845 0000

Product Details

- Ideal for Interferometry Applications
- Long Working Distances and High Numerical Apertures
- High-Quality Plan Apochromatic Design

Mitutoyo WLI Plan APO Infinity Corrected Objectives are high-resolution plan apochromatic objectives featuring high numerical apertures designed for use in white light interferometry applications. These objectives ensure long parfocal working distances of 60mm while maintaining a more compact and lightweight design. Each objective incorporates an interference fringe adjustment mechanism and internal beam splitter for precise measurements and control of the interference fringe pattern. Mitutoyo WLI Plan APO Infinity Corrected Objectives are available with magnifications ranging from 2.5 – 50x and are designed for use with 100mm focal length tube lenses. These objectives are ideal for white light interferometry applications such as Vertical Scanning Interferometry (VSI), 3D Surface Profiling, Dispersion & Reflection Measurement, and Medical Imaging.