

[See all 24 Products in Family](#)

266nm Flat Top Beam Shaper | πShaper 6_6_266

See More by [AdlOptica](#)



Stock #34-255 **2 In Stock**

- 1 + MRP ₹7,18,822

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1-4	₹7,18,822 each
Qty 5-10	₹6,47,131 each
Qty 11+	₹6,10,807 each
Need More?	Request Quote

Product Downloads

General

πShaper 6_6_266 **Model Number:**

Beam Shaper **Type:**

Flat Top **Style:**

Physical & Mechanical Properties

143.00 Length (mm):

<270 Weight (g):

39.00 Diameter (mm):

Optical Properties

6.3 Entrance Beam Diameter, $1/e^2$ (mm):

266 Design Wavelength DWL (nm):

250 - 275 Wavelength Range (nm):

50 mJ/cm² @ 5ns (typical) Damage Threshold, By Design:

5.2 Output Diameter, FWHM (mm):

50 mJ/cm² @ 5ns (typical) Damage Threshold, Pulsed:

Threading & Mounting

M27 x 1 Mounting Threads:

Regulatory Compliance

[Compliant](#) RoHS 2015:

[View](#) Certificate of Conformance:

[Compliant](#) Reach 250:

Germany Country of Origin:

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91-80-6845 0000

Product Details

- Convert Gaussian Beam Profile to Flat Top Profile
- Near 100% Efficiency
- No Internal Focusing Enables High Power Laser Input
- [AdlOptica Focal- \$\pi\$ Shaper Q Flat Top Beam Shapers](#) Also Available

AdlOptica π Shaper (piShaper) Flat Top Beam Shapers are refractive field mapping optical systems that convert collimated Gaussian input beams into collimated flat top beams with a uniform intensity distribution and flat phase front. Due to the field mapping optical design, the even intensity distribution of the converted beam is stable over great distances making it ideally suitable for holography, microscopy, system integration and ultrafast applications. With no internal focusing, they are also the perfect solution in applications such as material micromachining, welding, and engraving that require high power lasers. These AdlOptica π Shaper Flat Top Beam Shapers are offered in common YAG, fiber laser, and CO2 laser sources, operating over a defined wavelength range for laser tuning. Achromatic versions are designed to be used with multiple laser sources.

Note: Focusing a flat-top beam after a π Shaper results in loss of the flat top profile. [AdlOptica Focal- \$\pi\$ Shaper Q Flat Top Beam Shapers](#) are available for applications that require a focused flat top spot.

LASER OPTICS MADE BY EDMUND OPTICS®

[LEARN MORE](#)

Technical Information

Example of beam shaping for TEM₀₀ Laser

