


[See all 2 Products in Family](#)

27mm Diameter, Metric Thickness Gauge, Contact Reticle



Thickness Gauge

Stock #30-586 CLEARANCE **3 In Stock**

1 MRP ₹8,177

Price inclusive of all taxes

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1-4 | ₹8,177 each |
| Qty 5-9 | ₹7,689 each |
| Qty 10+ | ₹7,328 each |
| Need More? | Request Quote |

Product Downloads

General

Metric Thickness Gauge **Type:**

Physical & Mechanical Properties

27.00 ±0.05 **Diameter (mm):**

Thickness (mm):

2.28 ±0.127

±2 **Line to Line Accuracy (µm):**

Protective as needed **Bevel:**

<30 **Parallelism (arcsec):**

0.25 **Centering (mm):**

25.00 **Line Thickness (µm):**

±13 **Line Thickness Tolerance (µm):**

Optical Properties

±1 **Angle Tolerance (arcsec):**

60-40 **Surface Quality:**

3 - 4λ **Surface Flatness (P-V):**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Compliant **Reach 240:**

United States **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

Metric Scale: ½ Solid Bar, ½ Bracket Gauge: 13 line widths of 0.04mm to 0.10mm, 0.15mm, 0.20mm, 0.25mm, 0.30mm, 0.35mm, 0.40mm.

- Greater Stability than Film Reticles
- Low Reflection Chrome Pattern
- Compatible with 6 or 9X Comparators

These glass reticles offer greater stability than film reticles which can bend, warp, and easily be damaged. Patterns are low reflection chrome deposition for high contrast and easy readability. Markings are on the outside of the reticle, so the scales are always in direct contact with the object under view. This provides optimum focus and accurate measurements. Our 21mm and 27mm diameter reticles for use with our [6X and 9X comparators](#) and our 26mm and 35mm diameter reticles for use with our [Peak Measuring Loupes](#) and our [Peak Illuminated Magnifiers](#). Please note the field of view specified for the magnifiers before selecting a magnifier/reticle combination. For example, the 5/8" (16mm) field of view for a 12X comparator may not be suitable for use with a reticle that has a ¾" (20mm) scale if the full scale is needed.