


2.8mm² Two-Element Segmented Photodiode



Stock **#84-611** **9 In Stock**

- 1 + ₹6,750

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1-4 | ₹6,750 each |
| Qty 5-9 | ₹5,985 each |
| Qty 10+ | ₹5,310 each |
| Need More? | Request Quote |

Product Downloads

General

25.00 **Rise Time (ns):**

SPOT-3D **Model Number:**

Physical & Mechanical Properties

0.6x4.6 **Size of Active Area (mm):**

2.8 **Active Area (mm²):**

0.025 **Element Gap (mm):**

Electrical

Responsivity @ 970nm (AW):
Minimum: 0.6
Typical: 0.65

Capacitance @ V_R=-10V (pF):
7.00

Noise Equivalent Power NEP (W/ Hz^{1/2}):
9.9 x 10⁻¹⁵ @ -10 V, 970nm

Maximum Reverse Voltage (V):
30.00

Dark Current @ V_R=-10V (nA):
Maximum: 2
Typical: 0.13

Hardware & Interface Connectivity

Connector:
41 / TO-5

Environmental & Durability Factors

Operating Temperature (°C):
-40 to 100

Storage Temperature (°C):
-55 to 125

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Reach 223:
[Compliant](#)

Certificate of Conformance:
[View](#)

Product Details

- High Stability Over Temperature and Time
- Excellent Resolution, High Accuracy, Ultra-Low Dark Current
- Two or Four Separate Active Area Segments
- [Segmented InGaAs Photodiodes](#) Also Available

Segmented Photodiodes are designed for a wide variety of applications that require high stability and fast response times. Featuring position resolutions of greater than 0.1µm, Segmented Photodiodes are ideal for surface profiling, position measurement, alignment, or targeting. Segmented Photodiodes are segmented into either two or four separate active areas and have spectral response ranges from 350 – 1100nm. The segmented regions allow various measurement profiles on a single detector.