

2.8mW, 650nm, A Gated Cameo Laser



Stock #72-689 **1 In Stock**

- 1 + MRP ₹12,425

● Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1-9	₹12,425 each
Qty 10+	₹11,805 each
Need More?	Request Quote

Product Downloads

General

Mean Time To Failures MTTF @ 25° (hours):
≥50,000

Note:

Compatible with Interchangeable Optics:
[#73-168](#)
[#73-169](#)

#73-172
#73-175
#73-179

Diode **Type of Laser:**

IIIIR **Laser Class - CDRH:**

Physical & Mechanical Properties

14 x 14 **Dimensions (mm):**

15 **Weight (g):**

24 **Housing Length (mm):**

Optical Properties

650.00 **Wavelength (nm):**

3.1 **Beam Diameter (mm):**

<0.4 **Beam Divergence (mrad):**

Red **Color:**

25mm - ∞ **Focus Range (mm):**

Electrical

2.8 **Output Power (mW):**

±1.5 **Power Stability (%):**

Hardware & Interface Connectivity

Free Space **Output Type:**

JST 4 Pin **Connector:**

4.5 **Input Voltage (V):**

Environmental & Durability Factors

-10 to +45 **Operating Temperature (°C):**

-40 to +85 **Storage Temperature (°C):**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 240:**

United Kingdom **Country of Origin:**

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000 **Imported By:**

Product Details

- TTL Modulation up to 100kHz
- Compact 24 x 14 x 14mm Housing with M12 x 1 Threaded Barrel
- 635, 650, and 670nm Wavelength Options

Compact Gated Industrial Laser Diode Modules provide a high quality, cost effective OEM solution for a range of industrial applications. Featuring a gated CW laser output, these modules can achieve switching speeds up to 100kHz through the control input or they can be operated from low power TTL and microprocessors to achieve a simple, slow speed ON/OFF switching. An electrically isolated compact 24 x 14 x 14mm housing and M12 x 1 threaded barrel facilitates efficient cooling through good thermal contact and allows for easy integration into existing OEM laser systems. Compact Gated Industrial Laser Diode Modules are ideal for a wide range of industrial OEM applications including machine vision, inspection, positioning, and alignment. When operated within the appropriate temperature range (-10 to 55°C), these lasers can achieve long lifetimes with minimum mean time between failures (MTTF) ranging from ≥30,000 to ≥120,000 hours depending on wavelength.

Note: Interchangeable optics only compatible with A series Gated Cameo Lasers #72-688 and #72-689. C2 series lasers, #72-684 and #72-686, feature a fixed 2mm aperture lens, and S series lasers, #72-685 and #72-687, feature a fixed standard collimating lens that produces a beam size of 5 x 1.5mm.

