


## 2" Dia. Red Optical Cast Plastic Filter



Stock #43-943 **20+ In Stock**

- 1 + ₹1,635

**ADD TO CART**

Volume Pricing	
Qty 1-49	₹1,635 each
Qty 50-99	₹1,479 each
Qty 100-249	₹1,323 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Color Filter **Type:**

#### Physical & Mechanical Properties

50.80 **Diameter (mm):**

2.00 **Diameter (inches):**

Thickness (mm):  
1.50  
Dimensional Tolerance (mm):  
±0.3

## Optical Properties

Substrate:   
Thermoset ADC (CR-39®)  
Coating:  
Uncoated  
Color:  
Red  
Index of Refraction ( $n_d$ ):  
1.501  
Transmission (%):  
>20  
Abbe Number ( $v_d$ ):  
57.00

## Material Properties

Density ( $g/cm^3$ ):  
1.320 at 25°

## Environmental & Durability Factors

Operating Temperature (°C):  
100 Continuous, 130 for 1 Hour

## Regulatory Compliance


RoHS 2015:  
[Compliant](#)  
Certificate of Conformance:  
[View](#)  
Reach 242:  
[Compliant](#)  
Country of Origin:  
United States  
Importer:  
Edmund Optics India Private Limited

## Product Details

- Resistant to All Types of Chemicals and Solvents (Acetone, Acids, Alkali and Alcohols)
- Excellent Thermal Resistance
- Easily Drilled with High Speed Carbide Bits for Mounting

Optical Cast Plastic Color Filters have excellent thermal resistance. Traditionally, the limitations of plastic materials have made them unsuitable for demanding optical applications. However, advancement in plastic technology has produced filters with properties that can satisfy a variety of optical and environmental needs—and at half the weight of glass. Optical Cast Plastic Color Filters are ideal for use as environmental displays and filters. These filters, with their Thermoset ADC substrate, are also available in custom sizes, shapes, colors, and styles for qualified high volume OEM applications.

## Technical Information



## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more

- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts

---