

TECHSPEC[®] 2X, 110mm WD CompactTL[™] Telecentric Lens



110mm WD, 2X, In-Line Version (Left) and MS Version (Right)



Stock **#63-732** 4 In Stock

-

1

+

₹32,103

ADD TO CART

Volume Pricing	
Qty 1+	₹32,103 each
Need More?	Request Quote

Product Downloads

General	
CompactTL [™] Series	Series:
Edmund Optics [®]	Manufacturer:
Telecentric Lens	Type:
Physical & Mechanical Properties	

Fixed	Iris Option:
126.60	Length (mm):
126.60	Length excluding Threads (mm):
18.00	Maximum Diameter (mm):

58	Weight (g):

Optical Properties

4.4mm	Horizontal Field of View, 2/3" Sensor:
3.2mm	Horizontal Field of View, 1/2" Sensor:

2.4mm	Horizontal Field of View, 1/3" Sensor:
11.00	Maximum Image Circle (mm):

0.03	Numerical Aperture NA, Object Side:
±1	Working Distance Tolerance (mm):

5 (4)	Number of Elements (Groups):
0.065	Typical Telecentricity @ 588nm (°):

0.0567	Typical Distortion @ 588nm (%):
2X	Primary Magnification PMAG:

2.00	Telecentric Lens Magnification:
110	Working Distance (mm):

4.4 x 3.3	FOV @ Max Sensor Format, H x V (mm):
f/33	Aperture (f/#):

λ/4 MgF ₂	Coating:
±0.49mm (20% @ 20 lp/mm)	Depth of Field (mm):

2X	Magnification:
VIS	Lens Wavelength Range:

Sensor

2/3"	Maximum Sensor Format:
4.50	Pixel Size (µm):

Threading & Mounting

M25.5 x 0.50 (Female)	Filter Thread:
#88-212 (Required)	Filter Thread Adapter:

M16 x 0.5 (Female)	Front Thread:
C-Mount	Mount:

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:

Compliant	REACH 241:
China	Country of Origin:

Product Details


- 2/3", C-Mount Telecentric Lens
- Up to 2.3 MegaPixels, 4.5µm Pixel Size Sensors
- Small Telecentric Lens with Coaxial Illumination Options

TECHSPEC® CompactTL™ Telecentric Lenses are designed for applications with tight space constraints due to their ultra-compact design. These lenses feature a 2/3" sensor format and a variety of different working distance and magnification options. From single unit to high volume implementation, these lenses provide a great price to performance ratio. TECHSPEC® CompactTL™ Telecentric Lenses are perfect for integration into gauging systems due to their excellent telecentricity and low distortion. The fixed iris and lockable focus make these lenses ideal for implementation into factory floors and assembly lines, as they will remain fixed over time.


Technical Information




#63-732, 2X, 110mm WD CompactTL™ Telecentric Lens, Distortion Plot



#63-732, 2X, 110mm WD CompactTL™ Telecentric Lens, Relative Illumination Plot



#63-732, 2X, 110mm WD CompactTL™ Telecentric Lens, Telecentricity Plot



#63-732, 2X, 110mm WD CompactTL™ Telecentric Lens, Modulated Transfer Function (MTF) Plot, 110mm Working Distance, f33



#63-732, 2X, 110mm WD CompactTL™ Telecentric Lens, Depth of Field Plot, 110mm Working Distance, f33