

[See all 6 Products in Family](#)

2X 65mm WD, In-Line Illumination 1.2" Telecentric Lens



1.2" Sensor In-Line Illumination Telecentric Lenses

Stock **#72-173** **2 In Stock**

-

1

+

₹3,15,000

ADD TO CART

Volume Pricing	
Qty 1+	₹3,15,000 each
Need More?	Request Quote

Product Downloads

General	
1.2" Sensor In-Line Illumination Telecentric Lenses	Series:
Telecentric Lens	Type:
1/4" (0.312")	Compatible Light Guide/Source:
In-Line Illumination	Type of Illumination:

Physical & Mechanical Properties

160.00	Length (mm):
0.312	Ferrule Diameter (inches):

19.3	Maximum Diameter (mm):
------	------------------------

Optical Properties

7.25mm	Horizontal Field of View @ Max Sensor Format:
4.0mm	Horizontal Field of View, 2/3" Sensor:

3.4mm	Horizontal Field of View, 1/2" Sensor:
-------	--

19.30	Maximum Image Circle (mm):
-------	----------------------------

2X	Primary Magnification PMAG:
2.00	Telecentric Lens Magnification:

65.00	Working Distance (mm):
-------	------------------------

f/7.2	Aperture (f/#):
-------	-----------------

<0.01%	Distortion (%):
--------	-----------------

2X	Magnification:
----	----------------

VIS	Lens Wavelength Range:
-----	------------------------

Sensor

1.2"	Maximum Sensor Format:
2.74	Pixel Size (µm):

Threading & Mounting

N/A	Filter Thread:
C-Mount	Mount:

Regulatory Compliance

View	Certificate of Conformance:
----------------------	-----------------------------

Japan	Country of Origin:
-------	--------------------

Edmund Optics India Private Limited	Imported By:
-------------------------------------	--------------

Product Details

- 1.2" Max Sensor Format
- Fiber Optic Input for In-line Illumination
- Long Working Distance

1.2" Sensor In-Line Illumination Telecentric Lenses are designed for cameras with SONY IMX367, 530, and 540 or equivalent sensors allowing for large fields of view. These lenses are designed with an in-line illumination port that accepts a ¼" fiber optic light guide with incorporated M3 set screws in the in-line illumination port to light guide and include a lockable ring to rotate the lens and ensure alignment with the camera sensor. These telecentric lenses are designed to achieve high coaxial uniformity on 3µm, 24.5MP sensors and reduce parallax errors yielding maximum image quality with an excellent degree of measurement accuracy. 1.2" Sensor In-Line Illumination Telecentric Lenses are available in magnifications ranging from 0.5X–3.45X and offer low f/#s and a low distortion of <0.01%. These lenses are ideal for applications including machine vision, metrology, automotive and electronic inspection, measurement, and gauging.

Note: ¼" [Fiber optic light guides](#) are sold separately.