


TECHSPEC® 30 x 30mm Protected Silver, $\lambda/20$ Mirror



Stock #34-395 **20+ In Stock**

⊖ 1 ⊕ ₹16,971

ADD TO CART

Volume Pricing	
Qty 1-5	₹16,971 each
Qty 6-25	₹13,585 each
Qty 26-49	₹12,728 each
Need More?	Request Quote

Product Downloads

General

Flat Mirror **Type:**

Physical & Mechanical Properties

Commercial Polish **Back Surface:**

30.0 x 30.0 +0.00/-0.20 **Dimensions (mm):**

Clear Aperture (%):
90.00

Edges:
Ground, protective bevel as needed

Parallelism (arcsec):
30.00

Thickness (mm):
5.00

Length (mm):
30.00

Width (mm):
30.00

Optical Properties

Surface Flatness (P-V):
λ/20 (flatness pre-coating)

Substrate:
Fused Silica (Corning 7980)

Surface Quality:
20-10

Coating Specification:
R_{avg} >98% @ 450 - 2000nm
R_{avg} >98% @ 2000 - 10,000nm

Coating:
Protected Silver (450-10000nm)

Coating Type:
Metal

Wavelength Range (nm):
450 - 10000

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
View

Reach 247:
Compliant

Country of Origin:
United States

Importer:
Edmund Optics India Private Limited



Product Details

- Precision Fused Silica Substrate
- 20-10 Surface Quality
- Low Coefficient of Thermal Expansion

TECHSPEC® λ/20 First Surface Mirrors are polished to industry leading surface accuracy and quality specifications to minimize reflected wavefront error. These mirrors feature a precision fused silica substrate with a low coefficient of thermal expansion. Multiple coating options are available, allowing these mirrors to be integrated into applications spanning the visible through infrared spectra. TECHSPEC® λ/20 First Surface Mirrors are ideal for beam steering and reflection applications and are available in a variety of size, thickness, and coating options.

Note: Surface flatness is measured before coating.

Technical Information



Coating	Range (nm)	% Reflection	Coating	Range (nm)	% Reflection	Coating	Range (nm)	% Reflection	Coating	Range (nm)	% Reflection			
Protected Aluminum	0.4 - 0.7	85	Enhanced Aluminum	0.45 - 0.65	95	UV Enhanced Aluminum	0.25 - 0.45	89	Protected Gold	0.7 - 2.0	96	Protected Silver	0.45 - 2.0	98
	0.4 - 2.0	90		-	-		0.25 - 0.70	85		2.0 - 10.0	96		2.0 - 10.0	98

Coating Curves

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts
