

[See all 8 Products in Family](#)

300mm Dia x 42mm FL Alum. Coated, Parabolic Reflector



Stock #90-966 **2 In Stock**

- 1 + MRP ₹1,58,902

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-10	₹1,58,902 each
Qty 11-25	₹1,40,237 each
Qty 26-49	₹1,32,569 each
Need More?	Request Quote

Product Downloads

General

Parabolic Mirror **Type:**

Physical & Mechanical Properties

300.00 +0.0/-0.5 **Diameter (mm):**

No Center Hole **Center Hole Diameter (mm):**

130.0	Height (mm):
Optical Properties	
Metal	Coating Type:
Protected Aluminum (400-700nm)	Coating:
400 - 700	Wavelength Range (nm):
BOROFLOAT®	Substrate: <input type="checkbox"/>
0.140	Aperture (f#):
R _{avg} >85% @400 - 700nm	Coating Specification:
42.00	Focal Length FL (mm):
Regulatory Compliance	
View	Certificate of Conformance:
Japan	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:


Product Details

- Precision Polished Substrate
- Protected Aluminum and Cold Mirror Coating Options
- Ideal for Highly Divergent Light Sources
- [Precision Ellipsoidal Reflectors](#) Also Available


Precision Parabolic Reflectors are ideal for collimating a light source placed at the focal point of the mirror. The parabolic profile eliminates spherical aberration, allowing the light source to maintain its wavefront characteristics. These Precision Parabolic Reflectors feature very low *f*/#s, making them ideal for highly divergent light sources. The protected aluminum coating features broadband high reflection through the visible and IR spectra. The cold mirror coating reflects visible light while transmitting NIR, making it ideal for cold condensing applications.

Precision Parabolic Reflectors are precision polished, yielding exact aspheric profiles. These mirrors offer improved thermal stability and superior focusing efficiency versus commercially available press-molded reflectors. Typical applications include use as steppers for PCB, LCD, or PDP production, solar simulators, fiber optic illuminators, and projectors.

Technical Information



Diameter	Focal Length f	Center Hole Diameter d	Height H	Stock No.
100mm	12.5mm	—	45mm	#90-964
		—	45mm	#90-967
	19mm	30mm	32mm	#68-791
		—	32mm	#68-795
152mm	17mm	30mm	79mm	#68-792
	30mm	35mm	47mm	#90-965
220mm	100mm	—	33mm	#68-793
300mm	42mm	—	130mm	#90-966



;