

[See all 96 Products in Family](#)

300µm Aperture Diameter, Mounted, Precision Pinhole



300µm Aperture Diameter, Mounted, Precision Pinhole, #56-285

Stock **#56-285** [CONTACT US](#)

- 1 + MRP ₹8,475

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1-5	₹8,475 each
Qty 6-10	₹7,486 each
Qty 11+	₹6,921 each
Need More?	Request Quote

Product Downloads

General

Mounted **Type:**

Physical & Mechanical Properties

25 +0.4/-0.000 **Outer Diameter (mm):**

Construction:

Stainless Steel

300 **Fixed Aperture Diameter (μm):**

0.03 Nominal **Thickness (mm):**

± 5 **Aperture Tolerance (μm):**

± 125 **Aperture Centration (μm):**

Threading & Mounting

1.25 ± 0.05 **Mount Thickness (mm):**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Compliant **Reach 247:**

United States **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Available in Aperture Mounts for a Secure Mechanical Support
- Pinhole Sized Ranging from 1 to 1,000 Microns
- [High Power Apertures](#) Available

Unmounted Precision Pinholes

Precision Pinholes are high quality apertures centered to $\pm 0.002''$ (50 microns). They are constructed of stainless steel and are 3/8" (9.5mm) in diameter. Smaller diameter pinholes will reduce energy throughput, while larger diameter pinholes will pass more spatial noise. Precision pinholes have sizes ranging from 1 to 1,000 microns. Typical applications include leak detection, aerosol studies, holography, fiber optics guides, spatial filtering, research, and more.

Use the [Precision Pinhole Mount](#) to integrate unmounted pinholes into a variety of mechanical components easily.

Mounted Precision Pinholes

Precision Pinholes are available in aperture mounts for secure mechanical support. The mounts also fit into various optical assemblies. Each 9.5mm diameter pinhole is sealed within a 25mm diameter black-anodized aluminum mount. The mount is clearly labeled with a pinhole aperture diameter for easy identification.

Note: Aperture Centering to Mount ± 125 microns.

Edmund Optics offers a wide selection of precision pinholes for leak detection, aerosol studies, holography, fiber optic guides, spatial filtering, research, and more. These pinholes are available in a range of diameters and are ideal for controlling light propagation. Each pinhole is manufactured using high-accuracy techniques, providing consistent circular aperture geometry and high edge quality. Available in both mounted and unmounted formats, these pinholes support a variety of optical setups, from experimental labs to industrial environments.

Technical Information

