

[See all 12 Products in Family](#)

## 3.05 x 1.30mm, 0.192 ROC, 250µm Pitch, Fused Silica, 1 x 8 Linear Microlens Array



#21-175, 7.30 x 2.05mm, 0.575 ROC, 750µm Pitch, 1 x 8 Linear Microlens Array

Stock **#21-173** **5 In Stock**

MRP ₹13,578

**Price inclusive of all taxes**

**ADD TO CART**

Volume Pricing	
Qty 1-10	₹13,578 each
Qty 11-25	₹12,240 each
Qty 26-49	₹11,571 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

1 x 8 Linear Array **Type:**

Spherical **Lens Profile:**

Linear arrays are centered on the part and surrounded by inactive lenses. **Note:**

## Physical & Mechanical Properties

0.18 (of each lens) **Diameter (mm):**

0.14 (of each lens) **Clear Aperture CA (mm):**

3.05 x 1.30 ±0.05 **Dimensions (mm):**

0.192 ±3% **Radius R (mm):**

0.60 ±0.01 **Thickness (mm):**

## Optical Properties

**Fused Silica** (Corning 7980) **Substrate:**

BBAR (1260-1675nm), Lens Side **Coating:**

1260 - 1675 **Wavelength Range (nm):**

$R_{avg} \leq 0.3\%$  @ 1260 - 1675 **Coating Specification:**

1550 **Design Wavelength DWL (nm):**

250 ±0.3 **Pitch (μm):**

0.01 in glue ( $n_d = 1.5$ )  
0.015 **Working Distance (mm):**

Source: 0.0104  
Target: 0.085 **Mode Field Diameter (mm):**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

Switzerland **Country of Origin:**

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000 **Imported By:**

## Product Details

- Fused Silica and Silicon Substrates
- 1x4 and 1x8 Lens Array Configurations
- Ideal for Fiber Coupling and Collimating

Linear Microlens Arrays are available in fused silica and silicon substrates with linear arrays of either 4 or 8 lenses. Silicon has a high index of refraction, enabling short focal length, high-NA lens array designs, while fused silica offers excellent thermal stability and visible transmission to facilitate easy alignment. Linear Microlens Arrays are used to collimate and couple fiber arrays in fiber-to-fiber or laser-to-fiber applications, such as with semiconductor laser diodes. These lenses are AR coated for the near-infrared (NIR) with designs for 1310 and 1550nm, making them ideal for use with NIR lasers or in telecommunications.

## Technical Information

LINEAR MICROLENS ARRAYS

MFD, Source ( $\mu\text{m}$ )	MFD, Target ( $\mu\text{m}$ )	Working Distance ( $\mu\text{m}$ )	Design Wavelength (nm)	Substrate	Stock No. 1x4 Array	Stock No. 1x8 Array
10.4	85	15 in air, 10 in glue	1550	Fused Silica	#21-172	#21-173
9.2	250	600	1550	Fused Silica	#21-174	#21-175
9.2	80	286	1310	Silicon	#21-176	#21-177
10.4	250	1143	1550	Silicon	#21-178	#21-179
9.2	25	1202	1310	Silicon	#21-180	#21-181
3.0	250	304	1310	Silicon	#21-182	#21-183

