


[See all 3 Products in Family](#)

30mm Aperture, Acktar Blackened Laser Beam Trap

See More by [Acktar](#)



Acktar Blackened Laser Beam Trap



Stock #13-515 **20+ In Stock**

MRP ₹31,329

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-2	₹31,329 each
Qty 3+	₹30,267 each
Need More?	Request Quote

Product Downloads

General

Laser Beam Trap **Type:**

LBD-T-30 **Model Number:**

Physical & Mechanical Properties

Black Anodized Aluminum	Construction:
30mm (Dia.)	Aperture Size:
70.00	Length (mm):
41.5	Outer Diameter (mm):

Optical Properties

Vacuum Black & Metal Velvet	Coating:
100 - 10000	Wavelength Range (nm):

Electrical

20	Maximum Incident Power Density (W/cm²):
20	Maximum Power (W):

Threading & Mounting

55	Mount Diameter (mm):
M6 x 1.0	Mounting Threads:

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 250:
Israel	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- Coated for High Absorbance of Laser Light
- Tubular Beam Trap or Thin, Flat Beam Block Designs
- M6 Tapped Hole for Easy Post Mounting

Acktar Blackened Laser Beam Traps and Blocks feature proprietary coatings designed to absorb incident laser light from the ultraviolet (UV) to the long-wave infrared (LWIR) spectrums. These Acktar coatings can achieve a reflectivity factor of less than 10^{-6} (beam trap designs) and have laser damage thresholds up to 20 W/cm². An M6 tapped hole on both the beam trap and beam block designs allows for easy mounting to optical posts for integration into optical systems. Acktar Blackened Laser Beam Traps and Blocks are available in multiple sizes to accommodate small or large laser beams, increasing overall lab safety by reducing the risk of laser damage. The Flat Beam Block design features back screws for a 92mm cooling fan attachment, allowing for multiple blocks to be coupled to cover large areas.