

30W Deuterium / 5W Tungsten Lamp



30W Deuterium / 5W Tungsten Lamp, #87-300

Stock **#87-300** **1 In Stock**

-

1

+

₹3,24,000

ADD TO CART

Volume Pricing	
Qty 1-4	₹3,24,000 each
Qty 5+	₹2,88,000 each
Need More?	Request Quote

Product Downloads

General	
Note: Built-in power supply. AC power cord included. Fiber patchcord listed under Accessories tab sold separately.	
≥2000 / ≥10,000	Lamp Lifetime (hours):
Physical & Mechanical Properties	
220 x 187 x 130	Dimensions (mm):

Optical Properties

190 - 2500	Wavelength Range (nm):
------------	------------------------

Electrical

30W Deuterium 5W Tungsten	Output Power (W):
------------------------------	-------------------

Hardware & Interface Connectivity

SMA-905	Connector:
---------	------------

Regulatory Compliance

View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Designed for Use with [Spectrometers](#)
- Lamps Available for UV to NIR
- Xenon, Tungsten, or Deuterium Sources

Broadband Fiber-Coupled Light Sources are ideal for use in a variety of spectroscopy applications and for coupling with the Fiber Optic Reflectance Sphere. The pulsed Xenon source is designed for applications from the UV to visible. The Tungsten source is designed for applications in the visible to NIR. The Deuterium/Tungsten source is ideal for applications requiring wide spectral ranges from the UV to NIR.