

[See all 11 Products in Family](#)

3.10" High Brightness LED Diffuselite, 625nm, Strobed

See More by [Advanced Illumination](#)



Advanced Illumination Diffuselite LED Illuminators

Stock **#83-268** [CONTACT US](#)

-

1

+

₹1,05,570

ADD TO CART

Volume Pricing	
Qty 1+	₹1,05,570 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General	
DL194-625-I3S	Model Number:
50,000	LED Lifetime (hours):
12.00	Number of LEDs:
1.00	Number of Channels:

LED Illuminator	Type of Illumination:
Optional Manual Intensity Adjustment	Note:
	#86-887 and #89-555 are Available
Advanced Illumination	Manufacturer:
Diffuse	Geometry:
Strobed	Illumination Mode:
Physical & Mechanical Properties	
83.00	Height (mm):
133.00	Outer Diameter (mm):
89.00	Field Coverage (mm):
Optical Properties	
Red	Color:
625	Wavelength (nm):
13 - 50	Working Distance (mm):
Light Distribution (%): ±10 Edge to Edge (Dependent on Working Distance)	
Electrical	
30.00	Maximum Trigger Frequency (Hz):
30 - 300	Strobe Duration (µs):
Hardware & Interface Connectivity	
Flying Leads	Connector:
Power Supply Required and Sold Separately: USA: #66-855 Europe: #66-855 Japan: #89-513 Korea: #33-773 China: #66-855	Power Supply:
Environmental & Durability Factors	
0 to 65	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 233:
United States	Country of Origin:
Edmund Optics India Private Limited	Importer:

Product Details

- Ideal for Illuminating Curved Surfaces
- Well Suited for Inspecting Small, Specular Objects
- Variable Intensity and Strobed Options

Advanced Illumination Diffuselite LED Illuminators are ideal for inspecting small, reflective objects. LED intensity can be varied through the in-line potentiometer, and the projected light distribution edge to edge is ±10%. The 3.35" and 6.35" models feature high-brightness LEDs. The strobed models' flash duration is dependent on a trigger signal or potentiometer setting. The duration of the strobe can be adjusted from 30 - 300µs via a knob located in the back of the unit. The trigger input signal of the Advanced Illumination Diffuselite LED Illuminator is CMOS/TTL compatible. The maximum trigger frequency is 30 Hz.

Note: Required 24V power supply [#66-855](#). [Accessories for Advanced Illumination products](#) are available and sold separately.