

[See all 32 Products in Family](#)

355 & 532nm, 4-6mm Dia. Input Beam, Focal Flat Top Beam Shaper | Focal π Shaper_NUV_Q-5

See More by [AdiOptica](#)



Stock #12-238 [CONTACT US](#)

1 MRP ₹3,70,410

Price inclusive of all taxes

[ADD TO CART](#)

Volume Pricing	
Qty 1-4	₹3,70,410 each
Qty 5-10	₹3,33,131 each
Qty 11+	₹3,14,968 each
Need More?	Request Quote

Product Downloads

General

Model Number:
πShaper_NUV_Q-5

Type:

[#12-322](#) Compatible Adapter:

Physical & Mechanical Properties

29.00 Length (mm):

50 Weight (g):

20 Clear Aperture CA (mm):

42.00 Diameter (mm):

4 - 6 Input Beam Diameter, $1/e^2$ (mm):

Optical Properties

>99 Transmission (%):

355, 532 Design Wavelength DWL (nm):

335 - 560 Wavelength Range (nm):

TEM₀₀ Input Beam Mode:

<1.5 Typical Input Beam Mode Quality, M²:

±20 Input Beam Divergence (mrad):

Electrical

0.2 Maximum Input Power, CW (kW):

Threading & Mounting

M30 x 0.75 Inner Thread:

M30 x 0.75 Outer Thread:

Regulatory Compliance

[Compliant](#) RoHS 2015:

[View](#) Certificate of Conformance:

[Compliant](#) Reach 250:

Germany Country of Origin:

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Shapes Gaussian Beams to Airy Disk Profile
- Airy Disk is Focusable to Flat Top Spot
- Near 100% Efficiency
- [AdlOptica πShaper Flat Top Beam Shapers](#) Also Available

AdlOptica Focal-πShaper (piShaper) Q Flat Top Beam Shapers are used to transform Gaussian beams to flat-top profiles after focusing through a lens. This is accomplished by transforming the Gaussian beam to airy disk profiles immediately after the piShaper. These beam shapers feature a compact design with inner and outer threading, making them easy to integrate into equipment. AdlOptica Focal-πShapers are advantageous for beam shaping in micromachining applications, including scribing and PCB drilling, as well as micro-welding applications. Multiple models are available at Nd:YAG, Ti:Sapphire, and Infrared wavelengths with compatible input beam diameters as small as 2.5mm and up to 23mm.

Technical Information

