

TECHSPEC<sup>®</sup> 355nm, 50mm Diameter, OD 4.0 Notch Filter



TECHSPEC OD 4.0 Notch Filters

Stock **#67-124** **1 In Stock**

[Additional Bandwidths](#)

-

1

+

₹73,179

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | ₹73,179 each                  |
| Qty 6-25       | ₹56,986 each                  |
| Qty 26-49      | ₹53,172 each                  |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Type:

Notch Filter

Physical & Mechanical Properties

Diameter (mm):

50.00 +0.00/-0.10

Clear Aperture CA (mm):

|                                                                                                                                                     |                           |
|-----------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------|
| 42.5                                                                                                                                                |                           |
|                                                                                                                                                     | Thickness (mm):           |
| 5.00 ±0.1                                                                                                                                           |                           |
|                                                                                                                                                     | Construction:             |
| Mounted in Black Anodized Ring                                                                                                                      |                           |
|                                                                                                                                                     | Physical Durability:      |
| Adhesion per MIL-PRF-13830B, Section C.4.5.12<br>Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11<br>Cleaning per MIL-C-48497ASection 4.5.4.2 |                           |
|                                                                                                                                                     | Substrate Thickness (mm): |
| 3.5 ±0.5                                                                                                                                            |                           |

|                    |                                |
|--------------------|--------------------------------|
| Optical Properties |                                |
|                    | Optical Density OD (Average):  |
| ≥4.0               |                                |
|                    | Center Wavelength CWL (nm):    |
| 355.00             |                                |
|                    | Design Wavelength DWL (nm):    |
| 355                |                                |
|                    | Full Width-Half Max FWHM (nm): |
| 17.80              |                                |
|                    | Coating:                       |
| Hard Coated        |                                |
|                    | Surface Quality:               |
| 60-40              |                                |
|                    | Transmission (%):              |
| 90                 |                                |
|                    | Transmission Wavelength (nm):  |
| 325 - 475          |                                |
|                    | Reflection at CWL (%):         |
| 99                 |                                |
|                    | Transmitted Wavefront, RMS:    |
| <1λ                |                                |

|                      |                       |
|----------------------|-----------------------|
| Threading & Mounting |                       |
|                      | Mount Thickness (mm): |
| 5.0                  |                       |

|                                                                                                   |                           |
|---------------------------------------------------------------------------------------------------|---------------------------|
| Environmental & Durability Factors                                                                |                           |
|                                                                                                   | Environmental Durability: |
| Humidity per MIL-STD-810H, Section 507.6<br>Temperature per MIL-STD-810H, Section 501.7 and 502.7 |                           |

|                                     |                             |
|-------------------------------------|-----------------------------|
| Regulatory Compliance               |                             |
|                                     | RoHS 2015:                  |
| Compliant                           |                             |
|                                     | Certificate of Conformance: |
| View                                |                             |
|                                     | Reach 247:                  |
| Compliant                           |                             |
|                                     | Country of Origin:          |
| United States                       |                             |
|                                     | Imported By:                |
| Edmund Optics India Private Limited |                             |

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details


- >OD 4.0 Rejection of Laser Wavelength from 355nm to 1064nm
- Broad Transmission Range
- [OD 6.0 Notch Filters Also Available](#)
- Low Cost Alternative to Rugate Notch Filters

TECHSPEC® OD 4.0 Notch Filters are low-cost alternatives to Rugate Notch Filters. The filters feature narrow rejection bands of just ±2.5% of the center wavelength while offering greater than 99% reflection of the laser wavelength. These optical filters have a broad transmission range and are hard coated to guarantee performance that will not degrade with time, temperature, or humidity. TECHSPEC® OD 4.0 Notch Filters are mounted in a black anodized ring


engraved to ease filter handling, identification, and orientation. [OD 6.0 Notch Filters](#) are also available for purchase.

**Note:** These filters are optimized for high spectral performance rather than high Laser Induced Damage Thresholds (LIDT). A typical LIDT for these filters is 1 J/cm<sup>2</sup> @ 532nm, 10ns. Please [contact us](#) if you require a filter with a higher LIDT value.

## Technical Information



This graph is an example of a standard notch filter transmission curve. For specific wavelength data, please refer to the curve PDF attached to each respective part.



All mounted TECHSPEC® Optical Filters have an arrow on the side of the mount that points to the filter-coated surface for quick reference. Filter oriented such that arrow points to filter coated surface S1. Anti-reflective (AR) coating is applied to S2.

## Compatible Mounts