

TECHSPEC[®] 355nm CWL, 12.5mm Dia,1.3nm Bandwidth, OD 6 Laser Line Bandpass Filter



Stock **#68-927** 20+ In Stock

[Additional Bandwidths](#)

-

1

+

MRP ₹36,825

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹36,825 each
Qty 6-25	₹29,460 each
Need More?	Request Quote

Product Downloads

General	
Bandpass Filter	Type:
Physical & Mechanical Properties	
12.50	Diameter (mm):
8.5	Clear Aperture CA (mm):

Optical Properties	
0 ±2	Angle of Incidence (°):
1.3	Bandwidth (nm):
OD 5 Blocking Wavelength Range (nm) : 314.8 - 351.8 & 358.6 - 422.5	
OD 6 Blocking Wavelength Range (nm): 326.6 - 349.7 & 360.3 - 390.5	
≥6.0	Optical Density OD (Average):
355.00	Center Wavelength CWL (nm):
355	Design Wavelength DWL (nm):
2.50	Full Width-Half Max FWHM (nm):
Fused Silica (Coming 7980)	Substrate: ☐
Hard Coated	Coating:
60-40	Surface Quality:
≥80	Transmission (%):
$\lambda/4$ @ 633nm	Transmitted Wavefront, RMS:

Threading & Mounting	
3.5	Mount Thickness (mm):
Environmental & Durability Factors	
Environmental: MIL-STD-810F, sect. 507.4 Durability: MIL-C-48497A sect. 3.4.1	Durability:

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:
United States	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume




Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Over 90% Transmission at Design Wavelength
- Hard Coated Design
- Designed for Laser Applications

Available for use with common gas and solid state lasers, TECHSPEC OD 6 Laser Line Clean-Up Filters are designed to offer maximum transmission of stimulated emission, while eliminating noisy spontaneous emission. TECHSPEC OD 6 Laser Line Clean-Up Filters are ideal for laser-based fluorescence instrumentation, Raman spectroscopy, or for analytical or medical laser systems. Due to their steep edges, TECHSPEC Laser Line Clean-Up Filters are excellent complements to [TECHSPEC Notch Filters](#) or [TECHSPEC Raman Longpass Edge Filters](#).

Technical Information



Compatible Mounts