

[See all 24 Products in Family](#)

355nm Flat Top Beam Shaper | πShaper 6_6_350

See More by [AdlOptica](#)



Stock **#34-256** **2 In Stock**

-

1

+

₹5,61,600

ADD TO CART

Volume Pricing	
Qty 1-4	₹5,61,600 each
Qty 5-10	₹5,04,900 each
Qty 11+	₹4,77,000 each
Need More?	Request Quote

Product Downloads

General

πShaper 6_6_350

Model Number:

Beam Shaper

Type:

Flat Top

Style:

Physical & Mechanical Properties

143.00	Length (mm):
<270	Weight (g):
39.00	Diameter (mm):
Optical Properties	
6.3	Entrance Beam Diameter, 1/e ² (mm):
355	Design Wavelength DWL (nm):
330 - 380	Wavelength Range (nm):
50 mJ/cm ² @ 5ns (typical)	Damage Threshold, By Design: ☐
5.6	Output Diameter, FWHM (mm):
50 mJ/cm ² @ 5ns (typical)	Damage Threshold, Pulsed:
Threading & Mounting	
M27 x 1	Mounting Threads:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 250:
Germany	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Convert Gaussian Beam Profile to Flat Top Profile
- Near 100% Efficiency
- No Internal Focusing Enables High Power Laser Input
- [AdlOptica Focal-πShaper Q Flat Top Beam Shapers](#) Also Available

AdlOptica πShaper (piShaper) Flat Top Beam Shapers are refractive field mapping optical systems that convert collimated Gaussian input beams into collimated flat top beams with a uniform intensity distribution and flat phase front. Due to the field mapping optical design, the even intensity distribution of the converted beam is stable over great distances making it ideally suitable for holography, microscopy, and system integration. With no internal focusing, they are also the perfect solution in applications such as material micromachining, welding, and engraving that require high power lasers. These AdlOptica πShaper Flat Top Beam Shapers are offered in common YAG, fiber laser, and CO2 laser sources, operating over a defined wavelength range for laser tuning. Achromatic versions are designed to be used with multiple laser sources.

Note: Focusing a flat-top beam after a πShaper results in loss of the flat top profile. [AdlOptica Focal-πShaper Q Flat Top Beam Shapers](#) are available for applications that require a focused flat top spot.

LASER OPTICS

MADE BY EDMUND OPTICS®



Technical Information



