

TECHSPEC® 35mm DG Series Fixed Focal Length Lens



35mm Focal Length, #54-689

Stock **#54-689** [CONTACT US](#)

- 1 + MRP ₹60,762

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-49	₹60,762 each
Qty 50+	₹47,799 each
Need More?	Request Quote

Product Downloads

General

Product Family:
DG Series

Type:
Fixed Focal Length Lens

Imaging Lens Type:
Traditional Double-Gauss Style Lens

Physical & Mechanical Properties

Iris Option:

Variable	
50.10	Length (mm):
53	Maximum Diameter (mm):
53	Outer Diameter (mm):
142	Weight (g):
4	Maximum Rear Protrusion (mm):

Optical Properties

99.2mm - 23.0°	Horizontal Field of View @ Max Sensor Format:
Horizontal: 97.5mm - 22.9° Vertical: 73.1mm - 17.3° Diagonal: 121.9mm - 28.3°	Field of View at Max Sensor Format:
99.2mm - 23.0°	Horizontal Field of View, 1.1" Sensor:
89.4mm - 20.8°	Horizontal Field of View, 1" Sensor:
61.5mm - 14.4°	Horizontal Field of View, 2/3" Sensor:
50.3mm - 11.8°	Horizontal Field of View, 1/1.8" Sensor:
44.7mm - 10.5°	Horizontal Field of View, 1/2" Sensor:
40.5mm - 9.5°	Horizontal Field of View, 1/2.5" Sensor:
33.5mm - 7.9°	Horizontal Field of View, 1/3" Sensor:
25.1mm - 5.9°	Horizontal Field of View, 1/4" Sensor:
17.60	Maximum Image Circle (mm):
0.0158	Numerical Aperture NA, Object Side:
6 (4)	Number of Elements (Groups):
35.00	Focal Length FL (mm):
240 - ∞	Working Distance (mm):
f/4 - Closed	Aperture (f/#):
N4 MgF ₂	Coating:
N4 MgF ₂	Coating Specification:
19.23	Entrance Pupil Position (mm):
18.86	Object Space Principal Plane (mm):
-12.64	Image Space Principal Plane (mm):
0.52	Maximum Distortion (%):
-12.27	Exit Pupil Position (mm):
VS	Lens Wavelength Range:

Sensor

1.1"	Maximum Sensor Format:
2.74	Pixel Size (μm):

Threading & Mounting

M37.0 x0.75 (Female)	Filter Thread:
C-Mount	Mount:

Environmental & Durability Factors

Storage Temperature (°C):
-20 to +60

Regulatory Compliance

Compliant **RoHS 2015:**

Compliant **REACH 201:**

View **Certificate of Conformance:**

China **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91-80-6845 0000


Product Details

- Up to 4/3", C-Mount Lens
- Up to 9 MegaPixels, 2.8µm Pixel Size Sensors
- Double Gauss (DG) Lens with low distortion and high performance
- 18mm to 75mm Focal Length


TECHSPEC® DG Series Fixed Focal Length Lenses utilize a Double Gauss design to provide high-performance, low distortion, compact size, and exceptional value, while exceeding the performance of typically available fixed focal length lenses. These lenses feature a mechanical design that allows the focusing movement to be motorized by the user, yields image resolution greater than 100 lp/mm, and have a standard C-Mount. For most applications, the camera-lens combination can be attached to workstations using the ¼-20 mount provided on the camera. TECHSPEC® DG Series Fixed Focal Length Lenses include focus ring, manual iris, and set screws to facilitate a low profile integration in machine vision applications. Typical applications for the DG Series lenses include machine vision, assembly-line integration, and measurement and image analysis.

Note: [Industrial Boom Stands](#) are recommended for building vibration-free workstations.


Technical Information




#54-689, 35mm DG Series Fixed Focal Length Lens, Distortion Plot




#54-689, 35mm DG Series Fixed Focal Length Lens, Relative Illumination Plot




#54-689, 35mm DG Series Fixed Focal Length Lens, Working Distance versus Field of View Plot




#54-689, 35mm DG Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 240mm Working Distance, f4



#54-689, 35mm DG Series Fixed Focal Length Lens, Depth of Field Plot, 240mm Working Distance, f4



#54-689, 35mm DG Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 500mm Working Distance, f4



#54-689, 35mm DG Series Fixed Focal Length Lens, Depth of Field Plot, 500mm Working Distance, f4

Dimensions							
FL (mm)	A (mm)	B (mm)	C (mm)	D (mm)	E (mm)	F (mm)	Filter Thread (Dia. x Pitch)
18	48.0	32.3	4.6	40.0	-	2.5	M30.5 x 0.5
25	39.0	40.0	5.8	34.7	30.7	2.2	M30.5 x 0.5
35	45.0	50.1	11.6	40.0	42.1	0	M37.0 x 0.75
50	47.5	69.0	10.6	40.0	40.8	0	M39.0 x 0.5
75	54.0	116.2	19.2	46.0	67.7	0	M49.0 x 0.75

Compatible Cameras