

**TECHSPEC® 35mm f/2.8, UCi Series Fixed Focal Length Lens**



35mm UCi Series Fixed Focal Length Lens



Stock #33-898 **1 In Stock**

⊖ 1 ⊕ MRP ₹24,957

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹24,957 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

UCi Series **Product Family:**

Fixed Focal Length Lens **Type:**

No **IR Cut Filter:**

## Physical & Mechanical Properties

Fixed	<b>Iris Option:</b>
52.19	<b>Length (mm):</b>
26.5	<b>Maximum Diameter (mm):</b>
26.5	<b>Outer Diameter (mm):</b>
2.21	<b>Maximum Rear Protrusion (mm):</b>
52.19	<b>Maximum Length (mm):</b>

## Optical Properties

**Horizontal Field of View @ Max Sensor Format:**  
45.6mm - 11.9°

**Field of View at Max Sensor Format:**  
Horizontal: 45.6mm - 11.9°  
Vertical: 34.1mm - 8.9°  
Diagonal: 57.2mm - 14.9°

**Horizontal Field of View, 1/1.8" Sensor:**  
45.6mm - 11.9°

**Horizontal Field of View, 1/2" Sensor:**  
40.5mm - 10.6°

**Horizontal Field of View, 1/2.5" Sensor:**  
36.7mm - 9.6°

**Horizontal Field of View, 1/3" Sensor:**  
30.3mm - 7.9°

**Horizontal Field of View, 1/4" Sensor:**  
22.7mm - 6.0°

**Maximum Image Circle (mm):**  
9.00

**Numerical Aperture NA, Object Side:**  
0.026

**Number of Elements (Groups):**  
7 (5)

**Focal Length FL (mm):**  
35.00

**Working Distance (mm):**  
200 - ∞

**Aperture (f/#):**  
f/2.8

**Coating:**  
M4 MgF<sub>2</sub>

**Coating Specification:**  
M4 MgF<sub>2</sub>

**Entrance Pupil Position (mm):**  
34.01

**Object Space Principal Plane (mm):**  
49.25

**Image Space Principal Plane (mm):**  
-19.45

**Maximum Distortion (%):**  
-0.22

**Exit Pupil Position (mm):**  
-46.71

**Lens Wavelength Range:**  
VIS

## Sensor

**Optimized Sensor Format:**  
1/2.5"

**Maximum Sensor Format:**  
1/1.8"

**Pixel Size (μm):**  
1.85

## Threading & Mounting

**Filter Thread:**  
N/A

**Mount:**  
C-Mount

## Environmental & Durability Factors

Storage Temperature (°C):

-20 to +60

Type of Ruggedization:

Industrial (Fixed Aperture with Simplified Mechanics)

## Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

China

Imported By:

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Up to 1/1.8", C-Mount, S-Mount Lens
- Up to 12 MegaPixels, 1.85µm Pixel Size Sensors
- Instrumentation (UCi) versions of our UC Series Lenses with Streamlined Mechanical Designs and Fixed Apertures
- 4mm to 35mm Focal Length

TECHSPEC® UCi Series Fixed Focal Length Lenses utilize the same optics as the TECHSPEC UC Series Lenses and feature 4K resolution. These lenses are designed for small pixels  $\leq 2.2\mu\text{m}$  and offer a wide range of fixed apertures for a variety of applications. While optimized for 1/2.5" sensors, many focal length options can be used on sensors up to 1/1.8". TECHSPEC® UCi Series Fixed Focal Length Lenses are ideal for OEM applications that require small, robust, and lightweight imaging solutions.

**Note:** For adjustable aperture options, see our [TECHSPEC® UC Series Fixed Focal Length Lenses](#).

Edmund Optics has created a family of high-performance ultra-compact optical designs (the UC Series family) and developed 3 customized optomechanical solutions targeted for specific applications. These lens sub-families utilize the same optics as the UC Series lenses providing the same optical performance in a variety of optomechanical solutions to meet your application requirements:


**UC Series:** Features locking cam focus and iris adjustment in an ultra-compact design and is the most adjustable version of these optical designs; they are the typical high-quality machine vision lenses.

**UCi Series:** Simplified mechanics featuring fixed apertures with compact housing. [Industrial Ruggedization](#) for reduced size, cost, and locked focus.


**UCr Series:** All optics glued in place and a locking C-clamp focus ring. [Stabilized Ruggedization](#) for reduced pixel shift and improved focus stability.

**UCw Series:** Waterproof, designed to meet IEC [Ingress Protection](#) Code IPX7 to withstand exposure to water up to 1 meter depth for 30 minutes.


## Technical Information




#33-898, 35mm f/2.8, UCi Series Fixed Focal Length Lens, Distortion Plot




#33-898, 35mm f/2.8, UCi Series Fixed Focal Length Lens, Relative Illumination Plot




#33-898, 35mm f/2.8, UCI Series Fixed Focal Length Lens, Working Distance versus Field of View Plot




#33-898, 35mm f/2.8, UCI Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 400mm Working Distance, f2.8



#33-898, 35mm f/2.8, UCI Series Fixed Focal Length Lens, Depth of Field Plot, 400mm Working Distance, f2.8



#33-898, 35mm f/2.8, UCI Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 750mm Working Distance, f2.8



#33-898, 35mm f/2.8, UCI Series Fixed Focal Length Lens, Depth of Field Plot, 750mm Working Distance, f2.8

## Compatible Cameras