

## 3.5mm FL Wide Angle Low Distortion Lens



#68-669

Stock **#68-669** **12 In Stock**

MRP ₹96,111

**Price inclusive of all taxes**

**ADD TO CART**

### Volume Pricing

Qty 1+	₹96,111 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Product Family:  
Low Distortion Wide Angle Lenses

Type:  
Fixed Focal Length Lens

### Physical & Mechanical Properties

Iris Option:  
Fixed

Length (mm):  
38.20

42.0	<b>Maximum Diameter (mm):</b>
42	<b>Outer Diameter (mm):</b>
75.00	<b>Weight (g):</b>

## Optical Properties

180.00	<b>Field of View @ Min Working Distance (mm):</b>
82.4°	<b>Horizontal Field of View, 1/2" Sensor:</b>
66.9°	<b>Horizontal Field of View, 1/3" Sensor:</b>
8.00	<b>Maximum Image Circle (mm):</b>
3.50	<b>Focal Length FL (mm):</b>
100 - ∞	<b>Working Distance (mm):</b>
f/2.4	<b>Aperture (f/#):</b>
<0.4	<b>Distortion (%):</b>
<0.4	<b>Maximum Distortion (%):</b>
VS	<b>Lens Wavelength Range:</b>

## Sensor

1/2"	<b>Maximum Sensor Format:</b>
4.50	<b>Pixel Size (µm):</b>

## Threading & Mounting

M40.5 x 0.50	<b>Filter Thread:</b>
C-Mount	<b>Mount:</b>

## Regulatory Compliance

<a href="#">View</a>	<b>Certificate of Conformance:</b>
Japan	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Product Details

- Up to 1/2.5", C-Mount and CS-Mount options
- Up to 3 MegaPixel and Down to 1% Distortion
- No Refocusing from 100mm to Infinity
- 1.28mm to 40mm Focal Length

Low Distortion Wide Angle Lenses maintain high resolution for applications with long working distance requirements and can accommodate multi-megapixel camera sensors. The optical design of these low-distortion wide-angle lenses enables users to achieve less than 3% distortion over a 125° field of view, or less than 1% distortion over a 110° field of view. These lenses feature a locking screw for the manual iris enabling the use in high vibration environments. Low Distortion Wide Angle Lenses are ideal for security and surveillance, machine vision, or [factory automation](#) applications. These lenses do not require refocusing from 100mm to Infinity.

**Note:** Image will be flipped (180° rotation). Auto Iris Options require cameras with P-Iris or DC Iris control.