

35mW, 660nm Machine Vision Laser Dev Kit



Stock #72-690 **3 In Stock**

⊖ 1 ⊕ ₹1,35,000

ADD TO CART

Volume Pricing

Qty 1+	₹1,35,000 each
Need More?	Request Quote

Product Downloads

General

Mean Time To Failures MTTF @ 25° (hours):
≥100,000

Contents of Kit:

Lyte-MV-DCLM660nm, 35mW Machine Vision Laser
6 Interchangeable optics
USB Cable
Software
Heavy Duty Mounting Clamp
Focus Keys
Heavy Duty Carry Case

Diode **Type of Laser:**

IIIB **Laser Class - CDRH:**

Physical & Mechanical Properties

73.5 Long x 19 Dia **Dimensions (mm):**

44 **Weight (g):**

73.5 **Housing Length (mm):**

Optical Properties

660.00 **Wavelength (nm):**

5 **Beam Diameter (mm):**

< 0.5 **Beam Divergence (mrad):**

Red **Color:**

35mm - ∞ **Focus Range (mm):**

Electrical

35 **Output Power (mW):**

±3 **Power Stability (%):**

Hardware & Interface Connectivity

Free Space **Output Type:**

USB Micro B **Connector:**

5 **Input Voltage (V):**

Environmental & Durability Factors

-10 to +65 **Operating Temperature (°C):**

-10 to +80 **Storage Temperature (°C):**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 240:**

United Kingdom **Country of Origin:**

Edmund Optics India Private Limited **Imported By:**

Product Details

- Features a 660nm, 35mW Red Laser Diode
- USB Powered and Controllable via Computer
- Includes Mount, Six Different Projection Heads, and Software
- Ideal for Inspection, Measurement, and Control Applications

The Machine Vision Laser Development Kit is designed to serve as all-in-one industrial laser light source package for system integrators and developers in the machine vision and inspection industries. Featuring a high power 35mW, 660nm industrial laser diode, a heavy duty mounting clamp, and six interchangeable projection optics, this development kit provides all the necessary components and software for ease of setup and integration. In addition to the interchangeable projection optics, a focus key is included for manual laser focus adjustment, allowing the projection to fit working distances up to 5.5m. No external power supply is required, and when disconnected from the computer, the laser will retain its settings (such as modulation and output power), allowing for flexibility in system design and layout. The Machine Vision Laser Development Kit is ideal for use with industrial cameras for a range of inspection, measurement, and control applications. A rugged carrying case is included to securely store and transport all the kit components.

