

[See all 5 Products in Family](#)

38.1mm Dia., 1mm Thick, Uncoated, ISP Optics Barium Fluoride (BaF₂) Window | BF-W-38-1

See More by [ISP Optics](#)



Stock #24-497 **CLEARANCE** 11 In Stock

⊖ 1 ⊕ MRP ₹24,012

i Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹24,012 each
Need More?	Request Quote

Product Downloads

General

BF-W-38-1 **Model Number:**

Protective Window **Type:**

Crystal **Type of Window:**

Physical & Mechanical Properties

32.38	Clear Aperture CA (mm):
38.10 +0.00/-0.13	Diameter (mm):
1.00 ±0.13	Thickness (mm):
<3	Parallelism (arcmin):
Protective as needed	Bevel:
85	Clear Aperture (%):
Fine Ground	Edges:
0.34	Poisson's Ratio:
53	Young's Modulus (GPa):
82.00	Knoop Hardness (kg/mm ²):

Optical Properties

Uncoated	Coating:
Barium Fluoride (BaF₂)	Substrate: <input type="checkbox"/>
1.48	Index of Refraction (n _d):
40-20	Surface Quality:
81.78	Abbe Number (v _d):
Random	Axis Orientation:
200 - 12000	Wavelength Range (nm):
2λ	Surface Flatness (P-V):

Material Properties

4.89	Density (g/cm ³):
18.1	Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):

Environmental & Durability Factors

Maximum: 800	Operating Temperature (°C):
--------------	-----------------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:
Latvia	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- Excellent Transmission from 0.2 - 12µm
- Resistant to High-Energy Radiation
- High Transmission without AR Coatings

ISP Optics Barium Fluoride (BaF₂) Windows provide excellent transmission from 0.2- 12µm without the need for an Anti-Reflection (AR) coating due to its low index of refraction. Barium Fluoride has similar physical properties to Calcium Fluoride, but features higher resistance to high-energy radiation. This makes Barium Fluoride ideal for vacuum UV (VUV) applications such as thermography or laser spectroscopy where high radiation resistance is required. ISP Optics Barium Fluoride (BaF₂) Windows can be used up to 800°C in a dry environment, but prolonged exposure to moisture can degrade transmission in the ultraviolet range.

Note: These optical windows are very sensitive to thermal shock.

Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

;