

[See all 5 Products in Family](#)

# 38.1mm Dia., 2mm Thick, Uncoated, ISP Optics Barium Fluoride (BaF<sub>2</sub>) Window | BF-W-38-2

See More by [ISP Optics](#)



Stock #24-498 **CLEARANCE** 5 In Stock

1 MRP ₹24,527

● Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹24,527 each
Need More?	<a href="#">Request Quote</a>

## Product Downloads

### General

BF-W-38-2 **Model Number:**

Protective Window **Type:**

**Type of Window:**

Crystal

## Physical & Mechanical Properties

32.38 **Clear Aperture CA (mm):**

38.10 +0.00/-0.13 **Diameter (mm):**

2.00 ±0.13 **Thickness (mm):**

<3 **Parallelism (arcmin):**

Protective as needed **Bevel:**

85 **Clear Aperture (%):**

Fine Ground **Edges:**

0.34 **Poisson's Ratio:**

53 **Young's Modulus (GPa):**

82.00 **Knoop Hardness (kg/mm<sup>2</sup>):**

## Optical Properties

Uncoated **Coating:**

[Barium Fluoride \(BaF<sub>2</sub>\)](#) **Substrate:**

1.48 **Index of Refraction (n<sub>d</sub>):**

40-20 **Surface Quality:**

81.78 **Abbe Number (v<sub>d</sub>):**

Random **Axis Orientation:**

200 - 12000 **Wavelength Range (nm):**

2λ **Surface Flatness (P-V):**

## Material Properties

4.89 **Density (g/cm<sup>3</sup>):**

18.1 **Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):**

## Environmental & Durability Factors

Maximum: 800 **Operating Temperature (°C):**

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 240:**

Latvia **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Excellent Transmission from 0.2 - 12μm
- Resistant to High-Energy Radiation
- High Transmission without AR Coatings

ISP Optics Barium Fluoride (BaF<sub>2</sub>) Windows provide excellent transmission from 0.2- 12µm without the need for an Anti-Reflection (AR) coating due to its low index of refraction. Barium Fluoride has similar physical properties to Calcium Fluoride, but features higher resistance to high-energy radiation. This makes Barium Fluoride ideal for vacuum UV (VUV) applications such as thermography or laser spectroscopy where high radiation resistance is required. ISP Optics Barium Fluoride (BaF<sub>2</sub>) Windows can be used up to 800°C in a dry environment, but prolonged exposure to moisture can degrade transmission in the ultraviolet range.

**Note:** These optical windows are very sensitive to thermal shock.

## Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

;