

[See all 7 Products in Family](#)

38.1mm Dia. x 200mm FL, Uncoated, ISP Optics Zinc Selenide (ZnSe) PCX Lens | ZC-PX-38-200

See More by [ISP Optics](#)



Zinc Selenide Plano-Convex (PCX) Lenses



Stock **#24-956** CLEARANCE **5 In Stock**

-

1

+

₹26,009

ADD TO CART

Volume Pricing	
Qty 1+	₹26,009 each
Need More?	Request Quote

Product Downloads

General

Type:	
Plano-Convex Lens	
Model Number:	
ZC-PX-38-200	

Physical & Mechanical Properties

38.10 +0.00/-0.13	Diameter (mm):
Protective as needed	Bevel:
2.60 ±0.20	Center Thickness CT (mm):
<3	Centering (arcmin):
34.29	Clear Aperture CA (mm):
2.00	Edge Thickness ET (mm):

Optical Properties	
200.00 @ 10.6µm	Effective Focal Length EFL (mm):
Zinc Selenide (ZnSe), CVD Grade	Substrate: □
5.25	f/#:
0.10	Numerical Aperture NA:
Uncoated	Coating:
600 - 18000	Wavelength Range (nm):
199.39	Back Focal Length BFL (mm):
±2	Focal Length Tolerance (%):
281.20	Radius R ₁ (mm):
60-40	Surface Quality:
λ/20	Irregularity (P-V) @ 10.6µm:

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:
Latvia	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Low Dispersion and Absorption from 0.6 – 18µm
 - High Resistance to Thermal Shock
 - Uncoated or BBAR Coated for 8 – 12µm
- ISP Optics Zinc Selenide (ZnSe) Plano-Convex (PCX) Lenses are ideal for focusing or collimation of light in the Mid-Wave Infrared (MMIR) and Long-Wave Infrared (LWIR) spectrum. Featuring low absorption and high resistance to thermal shock, ZnSe is widely used in high power CO₂ laser systems. ZnSe is not recommended for harsh environments as it is a relatively soft material that scratches easily, and only has a Knoop Hardness of 120. ISP Optics Zinc Selenide (ZnSe) Plano-Convex (PCX) Lenses are available either uncoated or Broadband Anti-Reflection (BBAR) coated for increased transmission from 8-12µm.
- Note:** Special care should be taken when handling Zinc Selenide as it is a toxic material. Always wear rubber or plastic gloves to avoid risk of contamination.

Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

