

[See all 4 Products in Family](#)

38.1mm Dia. x 50.8mm FL, Uncoated, ISP Optics Calcium Fluoride (CaF₂) DCX Lens | CF-BX-38-50

See More by [ISP Optics](#)



Calcium Fluoride Double-Convex (DCX) Lenses

Stock **#24-767** CLEARANCE **3 In Stock**

-

1

+

₹36,990

ADD TO CART

Volume Pricing	
Qty 1-9	₹36,990 each
Qty 10+	₹33,300 each
Need More?	Request Quote

Product Downloads

General	
Type:	Double-Convex Lens
Model Number:	CF-BX-38-50
Physical & Mechanical Properties	

38.10 +0.00/-0.13	Diameter (mm):
<3	Centering (arcmin):
Protective as needed	Bevel:
12.50 ±0.20	Center Thickness CT (mm):
2.50	Edge Thickness ET (mm):
34.29	Clear Aperture CA (mm):


Optical Properties	
50.80 @ 5µm	Effective Focal Length EFL (mm):
Uncoated	Coating:
Calcium Fluoride (CaF ₂)	Substrate: ☐
60-40	Surface Quality:
λ	Irregularity (P-V) @ 632.8nm:
38.64	Radius R ₁ (mm):
38.64	Radius R ₂ (mm):
1.33	f/#:
±2	Focal Length Tolerance (%):
0.38	Numerical Aperture NA:
300 - 8000	Wavelength Range (nm):



Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:
Latvia	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Greater than 90% Transmission from 350nm-7µm
 - Low Index of Refraction
 - High Laser Damage Threshold
- ISP Optics Calcium Fluoride Double-Convex (DCX) Lenses are ideal for finite imaging applications requiring high transmission in the infrared wavelength spectrum. Calcium Fluoride features greater than 90% transmission from 350nm to 7µm and a low refractive index, allowing it to be used without an antireflective coating. In addition, its low absorption and high damage threshold makes it a popular choice for use with excimer lasers. ISP Optics Calcium Fluoride Double-Convex (DCX) Lenses offer low solubility and superior hardness compared to other fluoride-based substrates, allowing for use in harsh environments.

Technical Information





Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools