


38.1mm Diameter, Optical Cast Plastic Window



Stock #71-526 **17 In Stock**

MRP ₹2,424

i Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-49	₹2,424 each
Qty 50-99	₹1,926 each
Qty 100-199	₹1,817 each
Need More?	Request Quote

Product Downloads

General

Protective Window **Type:**

Physical & Mechanical Properties

1.50 ±0.01 **Diameter (inches):**

38.10 ±0.25 **Diameter (mm):**

Thickness (mm):
1.50 ±0.15

Optical Properties

Coating:
Uncoated

Substrate:
Thermoset ADC (CR-39®)

Index of Refraction (n_d):
1.501

Transmission (%):
>90 (typical)

Abbe Number (v_d):
59.2

Wavelength Range (nm):
400 - 1500

Material Properties

Density (g/cm³):
1.320

Environmental & Durability Factors

Operating Temperature (°C):
100 Continuous, 130 for 1 hour

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
[View](#)

Reach 242:
Compliant

Country of Origin:
United States

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Lightweight Alternative to Glass Windows
- Excellent Thermal and Chemical Resistance
- Higher Transmission than Similar Transparent Plastics

Clear Optical Cast Plastic Windows are a lightweight and durable option compared to a glass alternative. These windows have a high transmission and low haze, have 25 - 50 times greater abrasion resistance, and are resistant to all types of chemicals and solvents (acetone, acids, alkali and alcohols). Due to their construction, these windows are able to be drilled using a carbide bit for various mounting needs.

Clear Optical Cast Plastic Windows are uncoated, and are available in circular, rectangular, and square options.

Technical Information

