

[See all 34 Products in Family](#)

TECHSPEC® 3X, 2μm Vega® Broadband Beam Expander



3X, 2μm Low Power DA Beam Expander, #37-377

Stock **#37-377** **2 In Stock**

MRP ₹63,796

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-9	₹63,796 each
Qty 10-24	₹56,212 each
Qty 25-99	₹49,966 each
Need More?	Request Quote

Product Downloads

General

Beam Expander **Type:**

Note:
[Click here to learn the difference between fused silica 7979 and 7980](#)

Fixed Magnification **Style:**

Physical & Mechanical Properties

83.00 **Length (mm):**

78 **Weight (g):**

29.95 **Housing Diameter (mm):**

Optical Properties

10 **Entrance Aperture (mm):**

23 **Exit Aperture (mm):**

3X **Expansion Power:**

Substrate:
Fused Silica (Corning 7980)

>99 (nominal) **Transmission (%):**

0 **Angle of Incidence (°):**

Coating:
BBAR (1900-2100nm) & Laser V-Coat (1940-1950nm)

Broadband **Design Wavelength DWL (nm):**

<N/10 for 5.5mm input beam (nominal, $\lambda = \text{DWL}$) **Transmitted Wavefront, P-V:**

1900 - 2100 **Wavelength Range (nm):**

Coating Specification:
R_{avg} <0.1% @ 1940nm - 1950nm
R_{avg} <0.5% @ 1900nm - 2100nm
R_{avg} <0.25% @ 2000nm - 2100nm

Rotating Optics **Divergence Adjustment:**

Threading & Mounting

Input: Male M30 x 1 **Mounting Threads:**

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
View

Reach 251:
Compliant

United States **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- AR Coated for Broadband Tunable Laser Sources
- Fixed Magnifications Available from 1.5X to 20X
- Divergence Adjustable through Rotating Optical Design

TECHSPEC® Vega® Broadband Beam Expanders are designed for demanding tunable laser sources. These compact beam expanders are optimized at a wide range of wavelengths, with designs achieving N/10 transmitted wavefront error and no internally focusing ghost images for compatibility with high power lasers. TECHSPEC Vega Broadband Beam Expanders are easily integrated into prototype and advanced applications while maintaining quality across the adjustment range. They are ideal for medical laser applications employing Thulium and Holmium sources.

Note: The length of these beam expanders will change upon divergence adjustment, typically by 1 to 2mm from the specified length.

[TECHSPEC Vega® Laser Line Beam Expanders](#) are also available. For more cost sensitive applications, Edmund Optics also offers [TECHSPEC Scorpii® Nd:YAG Beam Expanders](#). For HeNe laser applications, [TECHSPEC Arcturus® HeNe Beam Expanders](#) are available. For higher precision applications where sliding optics are necessary, please see our [TECHSPEC Draconis® Nd:YAG Laser Line Beam Expanders](#) or [TECHSPEC Draconis® Broadband Beam Expanders](#). For broadband or ultrafast applications, [TECHSPEC Canopus® Reflective Beam Expanders](#) are available.

To learn more about the difference between the 2µm and 2µm low OH- content beam expanders, along with the different types of fused silica, review our [UV vs. IR Grade Fused Silica application note](#).

